




THIS DRAWING IS SUPPLIED FOR INFORMATION ONLY. DESIGN FEATURES, SPECIFICATIONS AND PERFORMANCE DATA SHOWN HEREON ARE THE PROPERTY OF THE AMPHENOL CORPORATION. NO RIGHTS OF REPRODUCTION ARE IMPLIED. ALL DIMENSIONS ARE SUBJECT TO NORMAL MANUFACTURING VARIATIONS.

Customer Drawing



订购信息 Ordering Information

PL18	3	X	-	30	1	-	70	-	5
键位及颜色 Key		高压互锁 HVIL		线缆大小 Cable Size					
"X" Key		0, 不带互锁 No HVIL		"70"=70mm ²					
"Y" Key		1, 带互锁 With HVIL		"50"=50mm ²					
				"35"=35mm ²					

规格参数 (Spec.):

1. 工作温度 Operating temperature: -40° C~+125° C.
2. 额定电流 Current rating (Connector Only): 300 A.
3. 额定电压 Operating voltage: 1000 VDC.
4. 耐电压 Dielectric withstanding voltage: 5000 VDC.
5. 防护等级 Protection class: IP67 & IP2X.
6. 电磁屏蔽 Shielding.
7. 机械寿命 Mating cycle: 50 Min.
8. 带自动二次锁扣 Automatic secondary lock.
9. 带高压互锁 Electrical interlock (HVIL).

REVISIONS					
REV	ZONE	ECO	DESCRIPTION	DATE	BY APPR
A	--	--	INITIAL RELEASE	05/06/16	KC GX
B	--	--	更改尾盖	10/19/16	SW RW

Standard Part List (With HVIL)

Model NO.	overall-diameter nominal (mm)	Dia Primary Insulation (mm)
PL183X-301-35-5	12.7±0.3	11.5±0.3
PL183Y-301-35-5		
PL183X-301-50-5	14.9±0.3	13.6±0.3
PL183Y-301-50-5		
PL183X-301-70-5	17.0±0.3	15.5±0.3
PL183Y-301-70-5		

Standard Part List (Without HVIL)

Model NO.	overall-diameter nominal (mm)	Dia Primary Insulation (mm)
PL183X-300-35-5	12.7±0.3	11.5±0.3
PL183Y-300-35-5		
PL183X-300-50-5	14.9±0.3	13.6±0.3
PL183Y-300-50-5		
PL183X-300-70-5	17.0±0.3	15.5±0.3
PL183Y-300-70-5		

AMPHENOL TP		Amphenol Technical Products International GZ					
		第三角投影 THIRD ANGLE PROJECTION	页面 SHEET	幅面 SIZE	版次 REV.	比例 SCALE	PART NAME: PwrLok 10mm 3POS Plug Conn
签名 SIGNATURE		日期 DATE	1 of 1	A3	B		DWG NO: PL183-300-5
制图 DRAWN	SW	10/19/16	UNLESS OTHERWISE SPECIFIED 1) All dimensions are in metric (mm). 2) Tolerances are as follows: 0 PL DEC ±1.00 1 PL DEC ±0.50 2 PL DEC ±0.20 Angles ±1°			CUST PART #: N/A	
审核 CHECKED						CUST REV. -	
批准 APPROVAL							