



Home |

Browse by Product Categories

dd to My TNB Stuff

- ▶ Cable Protection Systems
- ▶ Conduit Systems
- ▶ Fittings
- ▶ Power Connection & Control
- ▶ Connectors & Grounding
- ▶ Power & High Voltage
- ▶ Wire Termination
- ▶ Safety Technology
- ▶ Lighting
- ▶ Surge Protection
- ▶ Wire & Cable Management
- ▶ Boxes & Covers
- ▶ Fastening Systems
- ▶ Identification & Supplies
- ▶ Metal Framing & Cable Tray

CAD SUBMITTAL PACKAGE

Where To Buy

Enter Zip Code:

Enter Quantity:

Features

- DC operated, low coil consumption control circuit (1.4 to 2.8 W at pull-in and at holding)
- Hum-free coil
- Designed for rail or wall mounting

Application

- Space optimized control products mainly used for control functions or for small loads up to 4 amps

General

Series	KC6
Poles	4
Coil Type	DC
Auxiliary Contacts	4 NO

Dimension Information

H x W x D (inches)	2.26 x 2.07 x 1.84
--------------------	--------------------

Specifications

Coil Voltage	24V DC
--------------	--------

Packaging

Order Multiple	10
Inner Package	1
Outer Package	10
Package Height	2.13
Package Length	11.02
Package Width	4.53
T&B Sold in UOM	Each
T&B Weight Per UOM	39 lbs. per 100

Notes

- No auxiliary contact block permitted for mounting

HOME
Global Site
Report Issue

LOGIN
T&B Access (Dist only)
Suppliers
MyTNB

RESOURCES
Catalog PDFs
End User Toolkit
Solution Set Brochures
Vertical Market Brochures
Where To Buy

SUPPORT
Contact Us
Global Locations
Product Support
Tool Services
Legal/Privacy

COMPANY
About Us
Careers
Employees
News



© 2014 Thomas & Betts Corporation