





2 HOLES FOR
SADDLE WASHERS
AND CAPTIVE
SCREWS




2 HOLES FOR
MACHINE SCREWS
AND HEX NUTS



WASHER OR WASHER
PORTION OF INSERT

COMPRESSION INSERT TREE



SIZES: 1 2 3 4 5 6

THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION AND SUCH INFORMATION MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE OR USED FOR MANUFACTURING PURPOSES WITHOUT WRITTEN PERMISSION FROM AMPHENOL CANADA CORP.




REVISIONS			
REV	ECN, ERN NO.	DATE	APPRD.
A	PRODUCT DRAWING (EAR 13158)	OCT23/07	K.L.




#4-40 X 7/16" [11.11]
FILLISTER HEAD MACHINE
SCREW



#4-40 X 1/2" [12.70]
FILLISTER HEAD CAPTIVE
SCREW



#4-40 HEX NUT



#4 SADDLE WASHER

NOTES:

- 1.EACH BACKSHELL KIT CONTAINS 2 SHELL HALVES, 1 COMPRESSION INSERT TREE AND 2 OF EACH HARDWARE ITEM SHOWN.
- 2.BACKSHELL IS SUITABLE FOR SUBMINIATURE D CONNECTOR, C SIZE SHELL (37 POSITION STANDARD CONTACTS OR 62 POSITION HIGH DENSITY CONTACTS).
- 3.COMPRESSION JACKET INSERTS ARE DESIGNED FOR A CABLE DIAMETER RANGE OF .350 [8.89] TO .650 [16.51].
- 4.MATERIALS - ALL MATERIALS ARE RoHS COMPLIANT
SHELL - ZINC ALLOY, ZINC PLATED, HEXAVALENT CHROMIUM FREE FINISH.
INSERT TREE - BLACK THERMOPLASTIC, 75 DUROMETER
HARDWARE - STEEL, ZINC PLATED, HEXAVALENT CHROMIUM FREE FINISH

ASSEMBLY INSTRUCTIONS:

- 1.SELECT THE TIGHTEST INSERT THAT WILL FIT OVER THE CABLE, AND FEED THE CABLE THROUGH IT, PLACING THE END WITH THE SMALLER OD (THE END WITHOUT THE WASHER) TOWARDS THE CONNECTOR.
- 2.TERMINATE THE CABLE WIRES TO THE CONNECTOR.
- 3.CUT THE JACKET, FOLD THE SHIELDING BACK OVER THE OUTSIDE OF THE INSERT AND CUT IT JUST SHORT OF THE WASHER.
- 4.INSTALL SADDLE WASHERS, CAPTIVE SCREWS AND CONNECTOR.
- 5.PLACE THE WASHER IN OUTERMOST DEPRESSION IN CABLE EXIT AREA OF THE BACKSHELL AND SCREW SHELL HALVES CLOSED.

AMPHENOL PART NUMBER 17E-1657-37

DRAWN J. WOOD	DATE SEP28/07	Amphenol Canada Corp.	
DESIGNED			
CHECKED K. LAMBIE	OCT23/07		
I. E. APPRD.			
Q. A. APPRD.		17E SERIES METAL BACKSHELL FOR D-SUB CONNECTOR WITH C SIZE SHELL (37 STD OR 62 HD CONTACTS), STRAIGHT EXIT, #4-40 THREAD, RoHS COMPLIANT	
DWG. APPRD.			
ENG. REL. NO. EAR 13158			
REF.			
DIMENSIONS ARE IN INCHES [mm]	CODE ID. NO. 03554	DWG B	DRAWING NO. P-17E-1657-37
SCALE 1/1	WT. -----	SURF. -----	SHEET 1 OF 1