

TF

D-Sub connectors - Stamped and Formed Contacts

PRESS FIT STRAIGHT PCB TERMINATION

UL File: E149426

CHARACTERISTICS

Materials and Platings	
Shells	Steel, tin plated
Insulator	Glass-filled thermoplastic, UL 94V-0
Contacts	Brass, selected gold in mating area; 2.54µm (100µ") min. tin on termination area over 1.27µm (50µ") min. nickel
Rear inserts	Brass, 2.54µm (100µ") min. nickel plated
Boardlocks	Brass, 2.54µm (100µ") min. tin over 1.27µm (50µ") min. nickel plated
Screwlocks	Brass, 2.54µm (100µ") min. nickel plated

Electrical Data	
Current rating	3A
Voltage rating	300V AC
Withstanding voltage	1000V AC/rms 60Hz for one minute
Insulation resistance	1000MΩ
Contact resistance	25mΩ max

Climatic Data	
Operating temperature	-55°C to +125°C
Salt spray	24 hours

Mechanical Data	
Single contact insertion force	≤ 3.60 N
Single contact withdrawal force	≥ 0.2 N
Single contact insertion on board	≤ 100 N
Single contact withdrawal from board	≥ 20 N
Standard plating thickness	Gold flash 0.4µm (15µ") gold 0.76µm (30µ") gold

	Terminal Specification	Boardlock Specification
Finished Hole Cu Sn	1 (+0.09 -0.06) > 25 µm < 15 µm	3.1 +/- 0.05 mm Min 25 µm 5-15 µm

DESCRIPTION

The Amphenol "TF" series features eye of needle formed contacts, and insulator with closed entry contacts cavities.

This series gives you Amphenol's high standards of quality and reliability to meet all your technical requirements.

*Solderless
straight PCB
mount
connectors*


APPLICATIONS

- Industrial
- Telecom
- Any backplanes connections




Amphenol



TF / E4



Socket version




Plug version




For PCB holes diameters, see on page 1 (finished holes)

Nb OF CONTACTS	DIMENSIONS mm (inch)			
	A	B	C plug	C socket
9	30.81 (1.185)	24.99 (0.984)	16.92 (0.666)	16.33 (0.643)
15	39.14 (1.54)	33.32 (1.312)	25.50 (1.004)	24.66 (0.97)
25	53.04 (2.088)	47.04 (1.852)	28.96 (1.534)	38.38 (1.511)
37	69.32 (2.729)	63.50 (2.5)	55.42 (2.182)	54.84 (2.16)




Female





Size of connectors	Tooling PN
9	981 MC
15	982 MC
25	983 MC
37	984 MC

Male





Size of connectors	Tooling PN
9	985 MC
15	986 MC
25	987 MC
37	988 MC

Board mounting option



Flange mounting option



How to order

L 17TF ...

RoHS Compliant

Series

Number of contacts :
09-15-25-37

Contact type:
1 = pin
0 = socket

Contact plating
0 = gold flash
1 = 0.4 μm (15μ")
2 = 0.76 μm (30μ")

Flange mounting option :
0 = 3.10mm clear hole
1 = #4-40 threaded hole
2 = #4-40 threaded hole with
#4-40 UNC screwlock installed
4 = M3 threaded hole
5 = M3 threaded hole with
M3 screwlock installed

Board mounting option
0 = without boardlock
1 = with boardlock

Front shell plating
1 = tin over nickel

Do not hesitate to contact us for further information

Amphenol

Amphenol IT & Communication Products

Block A3/A4, The 4th Industrial District of
Industrial Headquarters, Dong Keng Road
Gong Ming Town, Shen Zhen China
Fax: +86(0)755 2754 9955

Technical Support

Tel: +86(0)755 2717 7945
Info-dsub@amphenol.com.cn
<http://www.dsubconnector.com>