




Rev	AWO #	Description	Date	Appr
-		RELEASED	8/11/05	

APPROVED: _____

DATE: _____ TITLE: _____



WIRE SIZE	CIRCUITS			
AWG	2	4-6	8-10	12-24
18	9 A	8 A	7 A	6 A
20	7 A	6 A	5 A	5 A
22	5 A	4 A	4 A	4 A
24	4 A	3 A	3 A	3 A

PART #	WIRE AWG	DIMENSIONS			
		C	D	E	F
DMH-A-C-F-R	22 ~ 24	.134 [3.4]	.130 [3.3]	.098 [2.5]	.090 [2.3]
DMH-B-C-F-R	18 ~ 22	.157 [4.0]	.177 [4.5]	.098 [2.5]	.090 [2.3]
DMH-C-C-F-R	16 ~ 18	.157 [4.0]	.177 [4.5]	.110 [2.8]	.106 [2.7]

SPECIFICATIONS:
Material: _____
Contacts: Brass
Plating: _____
Tin over Copper underplate overall
Electrical: _____
Operating voltage: 600 VAC max
Current rating: / Contact (See Chart)
Contact resistance: 10 mohms max
Environmental: _____
Lead free, RoHS compliant. **ROHS COMPLIANT**

ADAM TECH

909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

TITLE: CRIMP CONTACT, DMH SERIES
FEMALE, TIN PLATED, ON REELS

APPROVALS		DATE	SIZE		PART NO.	REV.
DRAWN	SS	8/11/05	X		DMH-X-C-F-R	-
CHECKED						
APPROVED						

REF: _____ SCALE: NTS SHEET 1 OF 1