


APPROVED: _____
 DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	7/20/16	
A		UPDATE SPEC.	1/25/19	AY/YC



CONTACT PIN	BRASS	GOLD
SHELL	BRASS	GOLD
GASKET	SILICONE	RED
RING	SUS 304	NATURAL
INSULATOR	PTFE	WHITE
BODY	BRASS	GOLD
DESCRIPTION	MATERIAL	FINISH

SPECIFICATIONS:

Electrical:
 Nominal Impedance: 50 ohms
 Frequency range: DC-6 GHz
 Working voltage: 335 VOLTS max.
 Proof voltage: 1,000 VOLTS
 Temperature Rating:
 Operating temperature: -65°C to +165°C
 Environmental:
 Lead free, RoHS compliant.



MAX. BOARD THICKNESS=0.85mm

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES HOLES .X ± .10 Ø.X ± .10 .XX ± .020 Ø.XX ± .015 .XXX ± .015 Ø.XXX ± .010			ADAM TECH INTERCONNECTS		909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710
APPROVALS DRAWN AY 7/20/16 CHECKED SY 7/20/16 APPROVED			TITLE RF CONNECTOR, SMA STR EDGE MOUNT		
SIZE X PART NO. RF2-154-T-17-50-G REF: S00277T			SCALE: NTS		REV. A SHEET 1 OF 1