

E7022PA004 Product Details

 [Share](#)
 [Print](#)
 [Email](#)


E7022PA004
(1423171-2)

TE Internal Number: 1423171-2

 [Active](#)

Time Delay Relays

[Not EU RoHS or ELV Compliant](#)

Product Highlights:

- 7000 Electropneumatic Timing - Nuclear Qualified Series
- Input Voltage = 125 VDC
- Contact Arrangement = 2 Form C, DPDT, 2 C/O
- Contact Rating = 1A @ 125 VDC
- Mounting Options = Mounting Holes, Panel Mount

[View all Features](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

 [Add to My Part List](#)
 [Request Sample](#)
 [Find Similar Products](#)
 [Buy Product](#)

Documentation & Additional Information

Product Drawings:

- None Available

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Series = 7000 Electropneumatic Timing - Nuclear Qualified
- Termination Type = Screw Terminal

Electrical Characteristics:

- Input Voltage (VDC) = 125
- Contact Rating = 1A @ 125 VDC

Contact Features:

- Mounting Options = Mounting Holes, Panel Mount
- Mode of Operation = Off-Delay
- Delay Time = 0.1 seconds to 1 second
- Type of Control = Knob
- Repeatability, Max. = ± 10%
- Approx. Dimensions (L x W x H) (mm [in]) = 82.55 x 78.49 x 107.95 [3.252 x 3.092 x 4.253]

Configuration Features:

- [Contact Arrangement](#) = 2 Form C, DPDT, 2 C/O
- Multiple Timing Ranges = Without

Industry Standards:

- [RoHS/ELV Compliance](#) = Not ELV/RoHS compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process

Conditions for Usage:

- Temperature Range (°C) = 21 - 40

Other:

- Brand = Agastat

Corporate Information

[Who We Are](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)

Quick Links

[Check Distributor Inventory](#)
[Cross Reference](#)
[Find Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat With Us](#)
[Find a Phone Number](#)
[Search Knowledge Base](#)
[Manage your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address 

