

E7022AH004 Product Details

[Share](#) | [Print](#) | [Email](#)


E7022AH004
(1423170-7)

TE Internal Number: 1423170-7

 [Active](#)

Time Delay Relays

[Not EU RoHS or ELV Compliant](#)

Product Highlights:

- 7000 Electropneumatic Timing - Nuclear Qualified Series
- Input Voltage = 120 VAC
- Contact - Arrangement = 2 Form C, DPDT, 2 C/O
- Contact Rating = 10A @ 120 VAC
- Mounting Options = Mounting Holes, Panel Mount

[View all Features](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#)
 [Request Sample](#)
 [Find Similar Products](#)
 [Buy Product](#)

Documentation & Additional Information	
<p>Product Drawings:</p> <ul style="list-style-type: none"> • None Available <p>Catalog Pages/Data Sheets:</p> <ul style="list-style-type: none"> • None Available <p>Product Specifications:</p> <ul style="list-style-type: none"> • None Available <p>Application Specifications:</p> <ul style="list-style-type: none"> • None Available <p>Instruction Sheets:</p> <ul style="list-style-type: none"> • Nuclear E7000 Series 2-Pole Timing Relay (PDF, English) <p>CAD Files:</p> <ul style="list-style-type: none"> • None Available 	<p>Additional Information:</p> <ul style="list-style-type: none"> • Product Line Information <p>Related Products:</p> <ul style="list-style-type: none"> • Tooling

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)	
<p>Product Type Features:</p> <ul style="list-style-type: none"> • Series = 7000 Electropneumatic Timing - Nuclear Qualified • Termination Type = Screw Terminal <p>Electrical Characteristics:</p> <ul style="list-style-type: none"> • Input Voltage (VAC) = 120 • Contact Rating = 10A @ 120 VAC <p>Contact Features:</p> <ul style="list-style-type: none"> • Mounting Options = Mounting Holes, Panel Mount • Mode of Operation = Off-Delay • Delay Time = 3 minutes to 30 minutes • Type of Control = Knob • Repeatability, Max. = ± 10% • Approx. Dimensions (L x W x H) (mm [in]) = 82.55 x 78.49 x 107.95 [3.252 x 3.092 x 4.253] 	<p>Configuration Features:</p> <ul style="list-style-type: none"> • Contact - Arrangement = 2 Form C, DPDT, 2 C/O • Multiple Timing Ranges = Without <p>Industry Standards:</p> <ul style="list-style-type: none"> • RoHS/ELV Compliance = Not ELV/RoHS compliant • Lead Free Solder Processes = Not relevant for lead free process <p>Conditions for Usage:</p> <ul style="list-style-type: none"> • Temperature Range (°C) = 21 - 40 <p>Other:</p> <ul style="list-style-type: none"> • Brand = Agastat

Corporate Information

- [Who We Are](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)

Quick Links

- [Check Distributor Inventory](#)
- [Cross Reference](#)
- [Find Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Search Knowledge Base](#)
- [Manage your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

