



+ RELAYS, CONTACTORS & SWITCHES

TIME DELAY RELAYS



✓ Active

TE CONNECTIVITY (TE)

## SCERX22FBA=SCERX22FBA

Agastat | SCE Specification Grade True Off-Delay Timing

SCERX22FBA

TE Internal Number: 3-1437463-8

Not EU RoHS Compliant

Not EU ELV Compliant

Type of Control Knob

Input Voltage (VAC) 48

Input Voltage (VDC) 48

Timing Range (Off-Time) (seconds) .5 – 15

Mode of Operation True Off-Delay

### DOCUMENTATION

Catalog Pages/Data Sheets

**5-1773450-5\_sec12\_SCE**

PDF

English

### FEATURES

Please review product documents or [contact us](#) for the latest agency approval information.

Product Type Features

**Product Category** Electromechanical Relays

**Relay Type** Time Delay

**Product Type** Relay

## Configuration Features

**Multiple Timing Ranges** Without

---

## Electrical Characteristics

**Input Voltage (VAC)** 48

**Input Voltage (VDC)** 48

**Timing Range (Off-Time) (seconds)** .5 – 15

**Actuating System** AC

---

## Contact Features

**Type of Control** Knob

**Delay Time** .5 – 15 seconds

**Contact Arrangement** 2 Form C, DPDT, 2 C/O

---

## Termination Features

**Termination Type** 8-Pin Octal Style Plug

---

## Mechanical Attachment

**Mounting Type** Socket

---

## Dimensions

**Dimensions (L x W x H) (Approximate)** 50 x 50 x 83 mm [ 1.97 x 1.97 x 3.27 in ]

---

## Usage Conditions

**Operating Temperature Range (°C)** -30 – 65

---

## Operation/Application

**Mode of Operation** True Off-Delay

---

## Other

**Repeatability (Max)** ±1%

---

## PRODUCT COMPLIANCE



Statement of Compliance

**Statement of Compliance**

PDF

---