

AMPHENOL RF PART NUMBER

082-96

N-Type Straight Clamp Plug for RG-8, RG-213, RG-225, 50 Ohm

Amphenol® RF



PRODUCT IMAGE
COMING SOON

PRODUCT OVERVIEW

RF Connector, N-Type Straight Clamp Plug for RG-8, RG-213, RG-225, 50 Ohm

Product Type	Connectors
Product Series	N-Type
Status	Active

PRODUCT SPECIFICATIONS

Gender	Plug
Orientation	Straight
Termination Style	Cable - Clamp
Impedance (Ohms)	50
Body Finish	Nickel
Body Material	Brass
Contact Finish	Silver
Contact Material	Brass
Contact Termination Style	Solder
Insulator Material	PTFE
Cable Group	G4
Cable Type	RG-213, RG-214, RG-225, RG-302, RG-393, RG-8, RG-87, RG-8A, RG-9, RG-9A, RG-9B
Coupling Mechanism	Threaded
Max Frequency (GHz)	11
Polarity	Standard
Thread Direction	Standard

Min. Temp. (Celsius)	-65
Max. Temp. (Celsius)	165
Mating Cycles	500
Military Qualified	Yes
Military Part Number	UG-21C/U

PRODUCT COMPLIANCE

Product compliance documentation, if available is listed below:

RoHS 2 (EU)	Compliant with Exemption 6C
-------------	-----------------------------