



SMC PRINTED CIRCUIT BOARD RECEPTACLES

| Connector Description | Terminal Type | MTG Hole | Plt. | Ins | Construction Notes | Dim. e | Amphenol Number | Fig. |
|--|---------------|----------|------|-----|--------------------|------------|---------------------|------|
| Printed Circuit Straight Jack Receptacle | Blunt Post | T | P19 | D1 | — | — | 903-420J-52P | 1 |
| Printed Circuit Straight Bulkhead Jack Receptacle | Blunt Post | T | P19 | D1 | — | .125 (3.2) | 903-421J-52P | 2 |
| Printed Circuit Right Angle Jack Receptacle | Blunt Post | T | P27 | D1 | Leak Tight | — | 903-378J-52A | 3 |
| Printed Circuit Right Angle Bulkhead Jack Receptacle | Blunt Post | T | P27 | D1 | Leak Tight | .125 (3.2) | 903-419J-52 | 4 |