

AMPHENOL RF PART NUMBER

## 000-34525

N Type Straight Clamp Plug for RG-59, RG-62, 50 Ohm

Amphenol® RF



PRODUCT IMAGE  
COMING SOON

### PRODUCT OVERVIEW

RF Connector, N Type Straight Clamp Plug for RG-59, RG-62, 50 Ohm

Product Type	Connectors
Product Series	N-Type
Status	Active

### PRODUCT SPECIFICATIONS

Gender	Plug
Orientation	Straight
Termination Style	Cable - Clamp
Impedance (Ohms)	50
Body Finish	Nickel
Body Material	Brass
Contact Finish	Silver
Contact Material	Brass
Contact Termination Style	Solder
Insulator Material	PTFE
Cable Group	E
Cable Type	Belden 8241, Belden 8263, Belden 8279, Belden 9209, RG-140, RG-210, RG-59, RG-59B, RG-62
Coupling Mechanism	Threaded
Max Frequency (GHz)	18
Polarity	Standard
Thread Direction	Standard

Min. Temp. (Celsius)	-65
Max. Temp. (Celsius)	165
Mating Cycles	500
Military Qualified	Yes
Military Part Number	UG-603A/U

---

## PRODUCT COMPLIANCE

Product compliance documentation, if available is listed below:

RoHS 2 (EU)	Compliant with Exemption 6C
-------------	-----------------------------