

## 103366 - 1 Product Details

No Image Available

**103366 - 1**

 [Active](#)

### .156 Inch AMPMODU .031 X .062 Mod I

[RoHS Compliant](#) (Statement of Compliance)

#### Product Highlights:

- ? [Housing](#)
- ? [Standard Profile](#)
- ? [Not Keyed](#)
- ? [Number of Positions = 6](#)
- ? [Not Stamped](#)

[View all Features](#)

#### Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

### Documentation & Additional Information

#### Product Drawings:

- ? [HOUSING, MOD I, DBL. ROW, .156 X .300 CENTER -LINE, 6...](#) (PDF, English)

#### Catalog Pages/Data Sheets:

- ? None Available

#### Product Specifications:

- ? [Interconnection System, AMPMODU Mod I, Standard Pressur](#) (PDF, English)

#### Application Specifications:

- ? [AMPMODU Mod I Receptacle Crimp Contact](#) (PDF, English)

#### Instruction Sheets:

- ? None Available

#### CAD Files: ([CAD Format & Compression Information](#))

- ? [3D Model](#) (IGES, Version O)

[List all Documents](#)

#### Additional Information:

- ? [Product Line Information](#)

#### Related Products:

- ? [Tooling](#)

### Product Features

(Please use the Product Drawing for all design activity)

#### Product Type Features:

- ? [Product Type](#) = Housing
- ? [Profile](#) = Standard
- ? [Keyed](#) = No
- ? [Number of Positions](#) = 6
- ? [Stamped](#) = No
- ? Comment = Contains latch and polarizing bars.

#### Body Related Features:

- ? Number of Rows = Dual
- ? Centerline, Matrix (mm [in]) = 3.96 x 7.62 [.156 x .300]

#### Housing Related Features:

- ? Housing Material = Polyester (PBT)
- ? Housing Color = Black
- ? Housing Flammability Rating = UL 94V -0

#### Industry Standards:

- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Not relevant for lead free process
- ? RoHS/ELV Compliance History = Always was RoHS compliant

#### Conditions for Usage:

- ? Terminate To = Wire

#### Other:

- ? Brand = AMP