


Product Details for 1116719 -3



1116719 -3

[Active](#)

2.16 [.085] IDC Connectors

[RoHS Compliant \(Statement of Compliance\)](#)

Product Highlights:

- ? Connector Kit
- ? Number of Positions = 50
- ? Standard Profile
- ? Plug
- ? Shielded

[View all Features](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- ? [plug kit,50 posn,post mld](#) (PDF, English)

Catalog Pages/Data Sheets:

- ? None Available

Product Specifications:

- ? None Available

Application Specifications:

- ? None Available

Instruction Sheets:

- ? None Available

CAD Files:

- ? None Available

Additional Information:

- ? [Product Line Information](#)

Related Products:

- ? [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- ? [Product Type](#) = Connector Kit
- ? [Number of Positions](#) = 50
- ? [Profile](#) = Standard
- ? [Gender](#) = Plug
- ? [Shielded](#) = Yes
- ? [Mating Connector Lock](#) = With
- ? Mating Connector Lock Type = Screwlocks
- ? [Slot Type Letter Code](#) = B
- ? [Wire/Cable Type](#) = 7 Strand, Solid
- ? [Cable Outer Diameter \(mm \[in\]\)](#) = 8.64 [0.340]
- ? Protective Cover = With
- ? Color = Black

Mechanical Attachment:

- ? [Panel Attachment](#) = Without

Body Related Features:

- ? [Wire Range \(Solid\) \(mm \[AWG\]\)](#) = 0.51 -0.40 [24 -26]
- ? [Wire Range \(Stranded\) \(mm ² \[AWG\]\)](#) = 0.20 ² [24]
- ? [Cable Exit Angle](#) = 90°

Housing Related Features:

- ? Housing Material = Polyphenylene Oxide

Industry Standards:

- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Not relevant for lead free process
- ? RoHS/ELV Compliance History = Always was RoHS compliant

Packaging Related Features:

- ? [Packaging Method](#) = Bulk Kit
- ? Inner Ferrule Inside Diameter (mm [in]) = 10.16 [0.400]
- ? Outer Ferrule Inside Diameter (mm [in]) = 12.70 [0.500]
- ? Packaging Quantity = 500

Other:

- ? Brand = AMP