


1217108 -1 Product Details



1217108 -1

[Active](#)

Surface Burner Connector System

[RoHS Compliant](#) (Statement of Compliance)

Product Highlights:

- ? [Clip](#)
- ? [Stainless Steel Material](#)
- ? [Oval Slot Mounting Hole Shape](#)
- ? [With FASTON Grounding Tab](#)
- ? [Hole Diameter = 4.57 mm](#)

[View all Features](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- ? [CLIP, HEAVY DUTY BURNER CONNECTOR](#) (PDF, English)

Catalog Pages/Data Sheets:

- ? None Available

Product Specifications:

- ? None Available

Application Specifications:

- ? [Heavy Duty Burner Connectors](#) (PDF, English)

Instruction Sheets:

- ? None Available

CAD Files:

- ? None Available

Additional Information:

- ? [Product Line Information](#)

Related Products:

- ? [Tooling](#)

[List all Documents](#)

Product Features

(Please use the Product Drawing for all design activity)

Product Type Features:

- ? [Product Type](#) = Clip
- ? [Material](#) = Stainless Steel
- ? Comment = With Ground Tab

Body Related Features:

- ? [Mounting Hole Shape](#) = Oval Slot
- ? FASTON Grounding Tab = With
- ? Hole Diameter (mm [in]) = 4.57 [0.180]

Industry Standards:

- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Not relevant for lead free process
- ? RoHS/ELV Compliance History = Always was RoHS compliant

Other:

- ? Brand = AMP