


178080 -1 Product Details



178080 -1

[Active](#)

MULTILOCK Connectors and Contacts

[RoHS Compliant](#) (Statement of Compliance)

Product Highlights:

- ? [Housing](#)
- ? [Plug](#)
- ? [040/070 Hybrid Plug Configuration](#)
- ? [Number of Rows = 3](#)
- ? [Number of Positions = 88](#)

[View all Features](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling Product Feature Selector](#)
- [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- ? [88 pos plug hsg assy impul mate conn](#) (PDF, English)

Catalog Pages/Data Sheets:

- ? None Available

Product Specifications:

- ? [XRER](#) (PDF, English)
- ? [IMPUL MATE CONNECTOR](#) (PDF, English)

Application Specifications:

- ? None Available

Instruction Sheets:

- ? [IMPUL-MATE* CONNECTOR](#) (PDF, English)

CAD Files:

- ? None Available

Additional Information:

- ? [Product Line Information](#)

Related Products:

- ? [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- ? [Product Type](#) = Housing
- ? [Gender](#) = Plug
- ? [Plug Configuration](#) = 040/070 Hybrid
- ? [Number of Positions](#) = 88
- ? [Mating Connector Lock](#) = With
- ? [Mating Connector Lock Type](#) = Center Lock
- ? [Mating Connector Number Positions](#) = 88
- ? [Keyed](#) = No
- ? Proprietary Name = MULTILOCK
- ? Connector Style = Impul -mate

Mechanical Attachment:

- ? [Panel Attachment](#) = Without

Body Related Features:

- ? [Number of Rows](#) = 3

Housing Related Features:

- ? [Housing Color](#) = White
- ? Housing Material = PBT

Industry Standards:

- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Not relevant for lead free process
- ? RoHS/ELV Compliance History = Always was RoHS compliant

Conditions for Usage:

- ? [Terminate To](#) = Wire

Other:

- ? Brand = AMP