



+ IDENTIFICATION AND LABELING

CALIBRATION LABELS



✓ Active

TE CONNECTIVITY QUP12YL

QUP12YL

TE Internal Number: 1878681-2

Always EU RoHS/ELV Compliant

Label Height **6.4 mm [.2519 in]**

Label Width **152.4 mm [6 in]**

Label Style **Wrap-Around Calibration**

Label Color **Yellow**

Label Finish **Matte**

Product Environmental Compliance

REACH Substance Communication Document

[RSCD_BBP](#)

PDF

English

Please review product documents or [contact us](#) for the latest agency approval information.

Product Type Features

Self-Laminating

Yes

Tamper Evident

No

Product Type

Q-CEE Label

Body Features

Material

Vinyl

Usage Conditions

Operating Temperature Range

-40 – 80 °C [-40 – 176 °F]

Operation/Application

Energy Product

No

Printer/Label Features

Label Height

6.4 mm [.2519 in]

Label Width

152.4 mm [6 in]

Product Availability	Label Style	Wrap-Around Calibration
	Region Label Color	Americas Yellow
Packaging Features	Label Finish	Matte
	Packaging Quantity	120
	Adhesive type	Permanent
Other	Label Type	Die-Cut (on Sheets)
	Configurator Part	No
	Printer Type	Hand writable

Product Compliance

[Statement of Compliance](#)

PDF

[VIEW ALL PRODUCT COMPLIANCE](#)

No compatible products found for QUP12YL