





LOC	DIST	REVISIONS 変更					
J	—	P	LTR	DESCRIPTION	DATE	DWN	APVD
			A	RELEASED	20MAR'13	J.C	T.N



P/N: 2201068-1 AS SHOWN
(NARROW TYPE WITH COVER)


1. MATERIAL
 - ① FRAME: STAINLESS STEEL
 - ② LOAD PLATE: STAINLESS STEEL
 - ③ HINGE CLEVIS: STAINLESS STEEL
 - ④ ACTIVE CLEVIS: STAINLESS STEEL
 - ⑤ HINGE LEVER: STAINLESS STEEL, 2.5 DIA
 - ⑥ ACTIVE LEVER: STAINLESS STEEL, 2.5 DIA
 - ⑦ HS STUD: STAINLESS STEEL
 - ⑧ CAPTIVE NUT: CARBON STEEL, FINISH: NI PLATING
 - ⑨ INSULATOR: POLYCARBONATE FILM PLUS ACRYLIC ADHESIVE LAYER
 - ⑩ CAPTIVE NUT COLLAR: CARBON STEEL, FINISH: NI PLATING
 - ⑪ DUST COVER: THERMO-PLASTIC, UL94V-0, BLACK
 - ⑫ RIVET: STAINLESS STEEL
 - ⑬ GASKET: LOW COMPRESSION SET SPONGE RUBBER
2. APPLICABLE SOCKET P/N: 2174988 SERIES
 - ③. INDICATED DATE CODE ON THE LOAD PLATE
 - ④. DO NOT OPEN WITH FORCE FROM OPEN END



83.9g	NARROW TYPE W/O COVER	1-2201068-1
88.2g	NARROW TYPE WITH COVER	2201068-1
WEIGHT	DESCRIPTION	P/N

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J.CHEN 20MAR2013		 TE Connectivity	
		CHK H.TAGUCHI 20MAR2013			
DIMENSIONS: 単位: ㎜		TOLERANCES, UNLESS OTHERWISE SPECIFIED: 一般公差		NAME 名称	
		APVD T.NAKASHIMA 20MAR2013 PRODUCT SPEC 製品規格			
MATERIAL 材料		ANGLES 仕上		ILM ASSY LGA2011-1	
		WEIGHT SEE TABLE		RESTRICTED TO —	
		CUSTOMER DRAWING		SCALE 原図	
				SHEET 1 of 2	
				REV A	

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
J	—		—	SEE SHEET 1	—	—	—



MAXIMUM OPEN ANGLES
(2201068-1, 1-2201068-1 AS SHOWN)

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN — CHK — APVD —	 TE Connectivity		
DIMENSIONS: 單位: 耗 mm	TOLERANCES, UNLESS OTHERWISE SPECIFIED: 一般公差	NAME 名稱			ILM ASSY LGA2011-1
	0-PLG ± ±0.3 1-PLG ± ±3* 2-PLG ± ±3* 3-PLG ± ±3* 4-PLG ± ±3*	PRODUCT SPEC 製品規格 —	RESTRICTED TO —		
	ANGLES 仕上	APPLICATION SPEC 取付適用規格 —			
MATERIAL 材料	FINISH 仕上	WEIGHT —	SIZE A2	CAGE CODE 00779	DRAWING NO 番号 C-2201068
CUSTOMER DRAWING			SCALE 尺度 NTS	SHEET 2 of 2	REV A

2201068

A