



CONNECTORS

STANDARD RECTANGULAR CONNECTORS



✓ Active

TE CONNECTIVITY (TE)

LATTICE CONN 12P R/ANGLE C/KIT

LATTICE PRODUCTS | LATTICE

176764-3

TE Internal Number: 176764-3

EU RoHS Compliant

EU ELV Compliant

Product Type Connector Kit

Number of Positions 12

Number of Rows 3

Operating Voltage (VAC) 250

Operating Temperature Range (°C) -20 – 105

[↓ PRODUCT DRAWING](#)
English

[↓ 3D PDF](#)

DOCUMENTATION

Product Drawings

AMP LATTICE CONN CABLE CLAMP KIT 12POS

PDF (TIFF AVAILABLE)

Japanese

AMP LATTICE CONN. R/A CABLE CLAMP KIT 12 POS.

PDF (TIFF AVAILABLE)

English

CAD Files

Customer View Model

2D_DXF.ZIP

English

Customer View Model

3D_IGS.ZIP

English

Customer View Model

3D_STP.ZIP

English

3D PDF

PDF

English

Product Specifications

Application Specification

Crimping Of AMP Lattice Contact

TIF

English

Crimping Of AMP Lattice Contact

PDF

English

Product Specification

AMP Lattice Connector

TIF

Japanese

AMP Lattice Connector

PDF

Japanese

Qualification Test Report

AMP Lattice Connector

PDF

English

AMP Lattice Connector

TIF

English

Instruction Sheets

Instruction Sheet (non U.S.)

AMP LATTICE CONNECTOR

TIF

English

AMP LATTICE CONNECTOR

PDF

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Kit Type Cable Clamp Kit

Product Type Connector Kit

Configuration Features

Number of Positions 12

Number of Rows 3

Electrical Characteristics

Operating Voltage (VAC) 250

Body Features

Cable Exit Angle 90°

Color Gray

Cable Clamp Material Steel

Mechanical Attachment

Screw Material Steel

Dimensions

Cable Outside Diameter 9.4 mm [.37 in]

Usage Conditions

Operating Temperature Range (°C) -20 – 105

Packaging Features

Packaging Quantity 25

Packaging Method Box

PRODUCT COMPLIANCE



Statement of Compliance

Statement of Compliance

PDF
