


 [Live Product Chat](#)



TE Part Number: 2 - 1393310 - 1

 Superseded

 [Add to Part List](#)
[Search for Replacement
Parts](#)

Always ELV Compliant (Find RoHS Compliant Alternates / Statement of Compliance)

Product Highlights:

- ? Receptacle
- ? Tab Fit = 6.35 x 0.81 mm
- ? Wire Range = 1.25 - 3.00 ² [16-12] mm [AWG]
- ? Insulation Diameter = 4.06 - 5.33 [.160 -.210] mm [in]
- ? Receptacle Style = Straight

[View all Features](#) | [Find Similar Products](#)

Quick Links

[Check Pricing & Availability](#)
[Search for Tooling](#)
[Product Feature Selector](#)
[Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- ? None Available

Catalog Pages/Data Sheets:

- ? None Available

Product Specifications:

- ? None Available

Application Specifications:

- ? None Available

Instruction Sheets:

- ? None Available

CAD Files:

- ? None Available

Additional Information:

- ## ? Product Line Information

Related Products:

- ## ? Tooling

Product Features

(Please use the Product Drawing for all design activity)

Product Type Features:

- ? Product Type = Receptacle
- ? Tab Fit (mm [in]) = 6.35 x 0.81 [.250 x .032]
- ? Insulation Diameter (mm [in]) = 4.06 -5.33
[.160 -.210]
- ? Receptacle Style = Straight
- ? Wire/Cable Type = Regular Wire
- ? Finish = None
- ? Material = Brass
- ? Insertion Force = Normal
- ? Insulation Support = With
- ? Crimp Type = F -Crimp
- ? FASTON = Yes
- ? For Housing Type = Single
- ? CSA Certified = Yes

Body Related Features:

- ? Wire Range (mm [AWG]) = 1.25 - 3.00 ² [16-12]
- ? Stock Thickness (mm [in]) = 0.41 [0.016]
- ? UL Rating = Recognized

Industry Standards:

- ? RoHS/ELV Compliance = ELV compliant
- ? Lead Free Solder Processes = Not reviewed for lead free solder process
- ? RoHS/ELV Compliance History = Always was ELV compliant

Packaging Related Features:

- ? Packaging Method = Strip

Other:

- ? Line = FASTIN -FASTON .250
- ? Brand = Tyco Electronics