



**+** TERMINALS & SPLICES

CRIMP WIRE PINS, TABS & FERRULES



✓ Active

TE CONNECTIVITY (TE)

## PIDG WIRE PIN

PIDG

165133

TE Internal Number: 165133

EU RoHS Compliant

EU ELV Compliant

Terminal Type Wire Pin

Wire Insulation Diameter (Max) 7.62 mm [ .3 in ]

Wire Insulation Diameter (in) .17 – .3

Heavy Duty No

Wire Size (AWG) 12 – 10

 **PRODUCT DRAWING**  
English

### DOCUMENTATION

Product Drawings

#### WIRE PIN PIDG

PDF (TIFF AVAILABLE)

English

Agency Approvals

CSA Certificate

#### PLASTI-GRIP INSULATED BUTT SPLICES, TERMNAL SPLICES AND TERMINALS REPORT

PDF

English

### FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

---

#### Product Type Features

**Barrel Type** Closed Barrel  
**Wire/Cable Type** Regular Wire  
**Insulated** Yes  
**Insulated Wire Support** Yes  
**Support Style** Insulation Support

---

#### Body Features

**Insulation Color** Yellow  
**Plating Material** Copper, Tin  
**Insulation Material** Nylon  
**Double Wire** No  
**Sleeve Material** Copper

---

#### Contact Features

**Terminal Type** Wire Pin  
**Terminal Orientation** Straight  
**Terminal Length** 9.9 mm [ .39 in ]

---

#### Termination Features

**Bullet Terminal** Without

---

#### Dimensions

**Wire Insulation Diameter (Max)** 7.62 mm [ .3 in ]  
**Wire Insulation Diameter (in)** .17 – .3  
**Wire Size (AWG)** 12 – 10  
**Wire Size (mm<sup>2</sup>)** 3 – 6  
**Wire Size (CMA)** 5180 – 13100  
**Barrel Inside Diameter** 8 mm [ .315 in ]  
**Overall Length** 31.3 mm [ 1.232 in ]

---

#### Operation/Application

**Heavy Duty** No

---

#### Packaging Features

**Packaging Method** Box  
**Packaging Quantity** 500

---

#### Other

**Barrel Color** Yellow

---

## PRODUCT COMPLIANCE



Statement of Compliance

## Statement of Compliance

PDF

---