

**Catalog**

- [Home](#)
- [Part Number Search](#)
- [Document Search](#)
- [CAD Model Search](#)
- [Text Search](#)
- [Alternate/Lead Free Part Search](#)
- [Multiple Part Comparison](#)
- [Alphabetical Search](#)
- [Brand Search](#)
- [Industry Product Search](#)
- [Product Type Search](#)
- [Product Family Search](#)
- [Competitor Cross Reference](#)
- [Lead Free Solutions](#)
- [Tool Search](#)
- [Help/Glossary](#)

**Ribbon Cable Connector System (AMP-LATCH)**
**↳ Ribbon Cable Connectors (AMP-LATCH)**
**AMP**    **3-216093-4**     [Active](#)
**Directive 2002/95/EC  
Compliant**
[RoHS Compliant](#)
**(Tyco Electronics P/N: 3-216093-4)**
[Search for Parts](#)

Document links for this part cannot be displayed. Your browser does not support inline frames or is currently configured not to display inline frames. Inline frames are supported in both Internet Explorer 5 and Netscape 6, as well as all later versions of these browsers.

Related Part Information		
General Information	eCommerce	Related Part Information
<ul style="list-style-type: none"> <li>✧ <a href="#">General Info</a></li> <li>✧ <a href="#">Sales Info</a></li> <li>✧ <a href="#">Assembly Subcontractors</a></li> </ul>	<ul style="list-style-type: none"> <li>✧ <a href="#">Pricing</a></li> <li>✧ <a href="#">Product Availability</a></li> </ul>	<ul style="list-style-type: none"> <li>✧ <a href="#">Tooling</a></li> </ul>

**Searchable Features:**

<b>Brand:</b>	AMP
<b>RoHS/ELV Compliance:</b>	RoHS compliant, ELV compliant
<b>Lead Free Solder Process:</b>	Wave solder capable to 240°C, Wave solder capable to 265°C
<b>Connector Type:</b>	DIP (Dual In Line Package)
<b>No. of Positions:</b>	34
<b>Gender:</b>	Plug
<b>Mating Polarization:</b>	No
<b>Terminate To:</b>	Printed Circuit Board
<b>Mounting Ears:</b>	Without

**Other Properties:**

<b>RoHS/ELV Compliance History:</b>	Always was RoHS compliant
<b>Centerline, Matrix (mm [in]):</b>	2.54 x 2.54 [.100 x .100]
<b>Contact Material:</b>	Phosphor Bronze
<b>Housing Material:</b>	Thermoplastic Polyester
<b>Housing Flammability Rating:</b>	UL 94V-0
<b>Housing Color:</b>	Gray
<b>Packaging Method:</b>	Loose Piece

<b>Contact Mating Area Plating:</b>	Tin
<b>Contact Termination Area Plating:</b>	Tin
<b>Special PCB Retention:</b>	No
<b>Cable Stop:</b>	Without
<b>Mating Connector Lock:</b>	Without
<b>Strain Relief:</b>	Without

---

[Copyright](#) and [Privacy Statement](#)

Visit [Tyco International, Ltd.](#)

[Products](#) | [Catalog](#) | [Brands](#) | [Industries](#) | [Commerce](#) | [Supplier](#) | [Contact Us](#) | [About](#) | [Home](#)