

Product Details for 3 - 88190 - 0



3-88190 -0

[Active](#)

Flexible Film Connectors

[RoHS Compliant \(Statement of Compliance\)](#)

Product Highlights:

- ? Housing
- ? 2.54 mm Centerline
- ? Connector Type = Standard
- ? Number of Positions = 10
- ? Number of Rows = Dual

[View all Features](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [View Mating Products \(2\)](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- ? [HOUSING, PIN, DBL ROW, W/DETENT SLOTS, MTG EARS, .10...](#) (PDF, English)

Catalog Pages/Data Sheets:

- ? None Available

Product Specifications:

- ? None Available

Application Specifications:

- ? [Flexible Flat Cable \(FFC\) Housings/w Contact Cavities...](#) (PDF, English)

Instruction Sheets:

- ? None Available

CAD Files: ([CAD Format & Compression Information](#))

- ? [3D Model](#) (STEP, Version AC)
- ? [3D Model](#) (IGES, Version AC)
- ? [2D Drawing](#) (DXF, Version AC)

[List all Documents](#)

Additional Information:

- ? [Product Line Information](#)

Related Products:

- ? [Tooling](#)
- ? [Mating Products \(2\)](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- ? [Product Type](#) = Housing
- ? [Connector Type](#) = Standard
- ? [Number of Positions](#) = 10
- ? [Mating Type](#) = Plug
- ? [Mating Connector Lock](#) = With
- ? Mating Connector Lock Type = Detent Windows
- ? [Mating Polarization](#) = With
- ? [Mounting Ears](#) = With
- ? Shrouded = Yes
- ? Flame Retardant = Yes
- ? Color = Black
- ? Comment = Housing sizes smaller than 20 position have only one detent window.; Use Extraction Tool No. 91092 -1 for round wire contacts.

Mechanical Attachment:

- ? [Panel Attachment](#) = With

Body Related Features:

- ? [Centerline \(mm \[in\]\)](#) = 2.54 [0.100]
- ? [Number of Rows](#) = Dual

Housing Related Features:

- ? Housing Material = Thermoplastic
- ? Housing Flammability Rating = UL 94V -0

Industry Standards:

- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Not relevant for lead free process
- ? RoHS/ELV Compliance History = Always was RoHS compliant

Conditions for Usage:

- ? [Terminate To](#) = FFC Cable

Other:

- ? Brand = AMP