

1057679-1 Product Details

 [Share](#)
 [Print](#)
 [Email](#)



TNC RF Connectors

 [Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- Connector - RF
- Jack
- Applies To Coaxial Cable
- Coaxial Cable Termination Type = Solder
- Coaxial Cable Type (RG/U or Mfg.) = 405 Semi-Rigid/2.16 [.085]

[View all Features](#)

Quick Links


- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

1057679-1

(3104-7985-00)

TE Internal Number: 1057679-1

 [Active](#)

 [View 3D PDF](#)

 [Add to My Part List](#)



[Request Sample](#)



[Find Similar Products](#)



[Buy Product](#)

Documentation & Additional Information

Product Drawings:

- [OST" STRAIGHT BULKHEAD CABLE JACK DIRECT SOLDER VERSION \(PDF, English\)](#)

Catalog Pages/Data Sheets:

- [TNC Connectors \(PDF, English\)](#)

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- [OST Bulkhead Feedthrough Cable Jack Direct Solder At... \(PDF, English\)](#)

CAD Files: ([CAD Format & Compression Information](#))

- [2D Drawing \(DXF, Version B\)](#)
- [3D Model \(IGES, Version B\)](#)
- [3D Model \(STEP, Version B\)](#)

[List all Documents](#)

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Product Type](#) = Connector - RF
- [Gender](#) = Jack
- [Body Style](#) = Straight
- [Body Material](#) = Brass
- Weatherproof = No
- [Solder Terminal](#) = With
- Grade = Military
- Dielectric Material = Solid PTFE

Mechanical Attachment:

- [Panel Mount Retention](#) = With
- Panel Mount Retention Type = Bulkhead

Electrical Characteristics:

- [Connector Impedance \(Ω\)](#) = 50

Termination Features:

- [Coaxial Cable Termination Type](#) = Solder

Body Features:

- [Body Plating](#) = Gold

Contact Features:

- Center Contact Plating = Gold

Configuration Features:

- [Coaxial Cable Type \(RG/U or Mfg.\)](#) = 405 Semi-Rigid/2.16 [.085]

Industry Standards:

- Government/Industry Qualification = No
- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

Conditions for Usage:

- [Applies To](#) = Coaxial Cable

Other:

- Brand = AMP

Corporate Information

[Who We Are](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)

Quick Links

[Check Distributor Inventory](#)
[Cross Reference](#)
[Find Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat With Us](#)
[Find a Phone Number](#)
[Search Knowledge Base](#)
[Manage your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

