

321017 Product Details

[Share](#) | [Print](#) | [Email](#)


321017

TE Internal Number: 321017
 Active

[View 3D PDF](#)

Ring and Spade Tongue Terminals

Always EU RoHS/ELV Compliant (Statement of Compliance)

- Product Highlights:**
- Terminal Shape = Ring Tongue
 - Receptacle Style = Straight
 - Body Style = PIDG
 - Barrel Type = Closed Barrel
 - Wire/Cable Type = Regular Wire
- [View all Features](#)

- Quick Links**
- ▶ [Check Pricing & Availability](#)
 - ▶ [Search for Tooling](#)
 - ▶ [Product Feature Selector](#)
 - ▶ [Contact Us About This Product](#)

[Add to My Part List](#) | [Request Sample](#) | [Find Similar Products](#) | [Buy Product](#)

Documentation & Additional Information

<p>Product Drawings:</p> <ul style="list-style-type: none"> WIRE TERMINAL PIDG - RING TONGUE WIRE SIZE: 26 - 22 (PDF, English) <p>Catalog Pages/Data Sheets:</p> <ul style="list-style-type: none"> None Available <p>Product Specifications:</p> <ul style="list-style-type: none"> None Available <p>Application Specifications:</p> <ul style="list-style-type: none"> None Available <p>Instruction Sheets:</p> <ul style="list-style-type: none"> None Available <p>CAD Files: (CAD Format & Compression Information)</p> <ul style="list-style-type: none"> 2D Drawing (DXF, Version N) 3D Model (IGES, Version N) 3D Model (STEP, Version N) 	<p>Related Products:</p> <ul style="list-style-type: none"> Tooling
---	---

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

<p>Product Type Features:</p> <ul style="list-style-type: none"> Terminal Shape = Ring Tongue Receptacle Style = Straight Barrel Type = Closed Barrel Wire/Cable Type = Regular Wire Insulation = Yes Insulation Support = Insulation Support Stud Diameter (mm [in]) = 3.02 [0.119] Stud Size = 4 Shape = RING-041 Heavy Duty = No Finish = Tin Color = Yellow <p>Electrical Characteristics:</p> <ul style="list-style-type: none"> Voltage (VAC) = 300 <p>Termination Features:</p> <ul style="list-style-type: none"> Wire/Cable Size (CMA) = 202 - 810 <p>Dimensions:</p> <ul style="list-style-type: none"> Insulation Diameter (mm [in]) = 2.08 [.082] Max. 	<p>Body Features:</p> <ul style="list-style-type: none"> Body Style = PIDG Wire Range (mm [AWG]) = 0.12-0.40² [26-22] Material = Copper Tongue Material Thickness (mm [in]) = 0.46 [0.018] Insulation Material = PVC <p>Contact Features:</p> <ul style="list-style-type: none"> Class = 2 <p>Industry Standards:</p> <ul style="list-style-type: none"> Government/Industry Qualification = No RoHS/ELV Compliance = RoHS compliant, ELV compliant Lead Free Solder Processes = Not relevant for lead free process RoHS/ELV Compliance History = Always was RoHS compliant <p>Packaging Features:</p> <ul style="list-style-type: none"> Packaging Method = Loose Piece <p>Other:</p> <ul style="list-style-type: none"> Brand = AMP
---	---

Corporate Information

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)
- [Terms & Conditions](#)
- [Privacy Policy](#)

Quick Links

- [Check Distributor Inventory](#)
- [Cross Reference Products](#)
- [Find Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Search Knowledge Base](#)
- [Manage Your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates


