


**Product Details for 352068 - 4**



**352068 - 4**

[Active](#)

**2mm Hard Metric PCB Mount Connectors  
(Z - PACK 2mm HM)**

[RoHS/Not ELV Compliant](#) (Find RoHS Compliant Alternates/Compliance Statement)

**Product Highlights:**

- ? Connector
- ? Connector Type = Type A
- ? Receptacle
- ? Interface Type = 2mm HM
- ? Contact Type = ACTION PIN Post

[View all Features](#)

**Quick Links**

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

**Documentation & Additional Information**

**Product Drawings:**

- ? [Z-PACK 2MM HM TYPE A - 25 COLUMNS PRE - SHIELDED RECEP...](#) (PDF, English)

**Catalog Pages/Data Sheets:**

- ? None Available

**Product Specifications:**

- ? None Available

**Application Specifications:**

- ? None Available

**Instruction Sheets:**

- ? None Available

**CAD Files:** ([CAD Format & Compression Information](#))

- ? [3D Model](#) (STEP, Version H)
- ? [3D Model](#) (IGES, Version H)
- ? [2D Drawing](#) (DXF, Version H)
- ? [Footprint](#) (IGES, Version O)

[List all Documents](#)

**Additional Information:**

- ? [Product Line Information](#)

**Related Products:**

- ? [Tooling](#)

**Product Features**

(Please use the Product Drawing for all design activity)

**Product Type Features:**

- ? [Product Type](#) = Connector
- ? [Connector Type](#) = Type A
- ? [Gender](#) = Receptacle
- ? [Number of Positions](#) = 110
- ? [PCB Mount Angle](#) = Right Angle
- ? [Mating Polarization](#) = With
- ? [Mating Polarization Method](#) = Multi -Purpose Center
- ? [Shielded](#) = Yes
- ? Comment = Female connector with pre installed shield.

**Mechanical Attachment:**

- ? [Board Mount](#) = Free Board
- ? [Module Length \(mm \[in\]\)](#) = 50.00 [1.968]
- ? [Crosstalk Version](#) = Standard
- ? Shield Style = Ground Return Shielding
- ? Shield Type = Upper

**Termination Related Features:**

- ? [Interface Type](#) = 2mm HM
- ? Termination End Plating = Tin -Lead over Nickel

**Body Related Features:**

- ? [Number of Rows](#) = 5
- ? [Grounding Contact](#) = Without
- ? Rows Loaded = A, D, E, C, B
- ? Number of Signal Contacts = 110
- ? CompactPCI Designation = J1, J4

**Contact Related Features:**

- ? Contact Type = ACTION PIN Post, Signal
- ? [Feedthrough Post Length \(mm \[in\]\)](#) = 3.71 [0.146]
- ? [CompactPCI](#) = No
- ? [Contact Mating Area Plating](#) = Gold (50) over Nickel (50)
- ? Contact Style = Short Tail
- ? Contact Material = Phosphor Bronze

**Housing Related Features:**

- ? Housing Material = Glass -Filled Polyester
- ? Housing Color = Gray
- ? Housing Flammability Rating = UL 94V -0

**Industry Standards:**

- ? [RoHS/ELV Compliance](#) = RoHS/Not ELV Compliant
- ? [Lead Free Solder Processes](#) = Not relevant for lead free process
- ? RoHS/ELV Compliance History = Always was RoHS not ELV compliant

**Other:**

- ? Brand = AMP