


 [Live Product Chat](#)



TE Part Number: 3-826629-2

✓ Active

 Add to Part List

 Always EU RoHS/ELV Compliant (Statement of Compliance)

- Header
- Header Type = Breakaway
- Number of Rows = Single
- Number of Positions = 32
- Mating Post Length = 6.70 mm

[View all Features](#) | [Find Similar Products](#)

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

- [AMPMODU II STIFTELEISTEN, EINREIHIG](#) (PDF, German)

- None Available

- None Available

- None Available

- None Available

- 2D Drawing (DXF, Version Y2)
- 3D Model (IGES, Version Y2)
- 3D Model (STEP, Version Y2)

- Product Line Information

- Tooling

List all Documents

- Product Type = Header
- Number of Positions = 32
- Mount Angle = Vertical
- PCB Retention Feature = No
- Surface Mount Compatible = No
- Board Standoff = Without
- Mounting Ears = Without
- Mating Connector Lock = Without
- Profile = Standard

- Mating Post Length (mm [in]) = 6.70 [0.264]
- Panel Attachment = Without

- Termination (Solder) Post Length (mm [in]) = 3.20 [0.126]
- Solder Tail Contact Plating = Tin

- Header Type = Breakaway
- Number of Rows = Single
- Centerline, Matrix (mm [in]) = 2.54 [.100]
- Selectively Loaded = No
- Mount Type = PC Board

- Contact Mating Area Plating Material = Gold (30)
- Contact Material = Phosphor Bronze

- Housing Material = Thermoplastic Polyester
- Housing Flammability Rating = UL 94V-0

- RoHS/ELV Compliance = RoHS compliant, ELV compliant
- Lead Free Solder Processes = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- RoHS/ELV Compliance History = Always was RoHS compliant

- High Temperature Housing = No

- High Speed Serial Data Connector = No

- Brand = AMP