









SECTION A - A



## REVISIONS

| P | LTR | DESCRIPTION               | DATE      | DWN | APVD |
|---|-----|---------------------------|-----------|-----|------|
|   | B12 | REVISED PER ECR-16-009157 | 29JUN2016 | BW  | RS   |
|   | B13 | ECR-16-013951             | 10OCT2016 | KD  | RR   |
|   | C   | ECR-17-015100             | 25OCT2017 | KD  | RR   |
|   | C1  | ECR-17-015894             | 31OCT2017 | KD  | RR   |

- 1) TYPICAL CAVITY SCAVITY SUITABLE FOR:  
FASTIN-FASTON TAB CONTACTS 6.3 mm SRS:  
P/N: 60294, 0.3-0.8 mm2 WIRE RANGE  
160691, 0.3-0.8 mm2 WIRE RANGE  
AMPLIVAR CONTACTS:  
P/N: 141051, 0.1-0.5 mm2 WIRE RANGE  
142411, 0.3-1.6 mm2 WIRE RANGE  
MAX. INSULATION DIA. 2.8 mm,  
MAX. INSULATION CRIMP WIDTH 3.3 mm.
- 2) PA66 UNFILLED, UL 94-V2, NATURE COLOUR  
ACCORDING TO IEC 60335-1 NORM. EDITION 4
- 3) PA66 UNFILLED, UL 94-V2, NATURAL COLOUR
- 4) TRADEMARK "LOGO" AND  
TYCO ELECTRONICS "PART NUMBER"  
OPTIONAL POSITION.
- 5) CIRCUIT IDENTIFICATION NUMBERS, 1 TO 3
- 6) POLARIZATION KEYS DIMENTIONS AND POSITIONS  
ARE ACCORDING TO "RAST 5" NORM  
RAST CODE 03-A & 03-1.
- 7) PA66 UNFILLED, UL 94-V0, NATURAL COLOUR
- 8) PA66 UNFILLED, UL 94-V0 GWT, NATURAL COLOUR
- 9) PRELIMINARY - NOT RELEASED FOR PRODUCTION
- 10) PA66 UNFILLED, UL94-V0 GWT, NATURAL COLOUR
- 11) -
- 12) PA66 UNFILLED, UL94-V0 GWT, BLUE COLOR
- 13) ONLY FOR 293008-3, ADD UL LOGO

|         |             |    |            |
|---------|-------------|----|------------|
| BLUE    | SEE NOTE 12 | 9  | 3-293008-1 |
| NATURAL | SEE NOTE 10 | 9  | 2-293008-2 |
| NATURAL | SEE NOTE 10 | 9  | 2-293008-1 |
| NATURAL | SEE NOTE 2  |    | 1-293008-1 |
| NATURAL | SEE NOTE 10 |    | 293008-6   |
| NATURAL | SEE NOTE 8  |    | 293008-5   |
| NATURAL | SEE NOTE 7  | 13 | 293008-3   |
| NATURAL | SEE NOTE 3  |    | 293008-2   |
| NATURAL | SEE NOTE 2  |    | 293008-1   |
| COLOUR  | MATERIAL    |    | TE P/N     |




TE Connectivity

|      |                                                                                      |
|------|--------------------------------------------------------------------------------------|
| NAME | 3 POS. FASTIN-FASTON Connector<br>TAB HOUSING, RAST 5<br>0.8-1.0 MM THK. PANEL MOUNT |
|------|--------------------------------------------------------------------------------------|


|      |           |            |               |    |     |
|------|-----------|------------|---------------|----|-----|
| SIZE | CAGE CODE | DRAWING NO | RESTRICTED TO |    |     |
| A2   | -         | C-293008   | -             |    |     |
|      |           | SCALE      | SHEET         | OF | REV |
|      |           | 5          |               | 2  | C1  |

| P | LTR | DESCRIPTION | DATE | DWN | APVD |
|---|-----|-------------|------|-----|------|
|   | -   | SEE SHEET 1 | -    | -   | -    |
|   |     |             |      |     |      |
|   |     |             |      |     |      |
|   |     |             |      |     |      |


POLARIZATION SCHEME




293008-X




1-293008-X



2-293008-1



2-293008-2



3-293008-1

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN  
H. YAALI  
CHK  
C. TARTARI  
APVD  
-

DIMENSIONS:  
mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:  
0 PLC ±  
1 PLC ±0.3  
2 PLC ±  
3 PLC ±  
4 PLC ±  
ANGLES ±1°  
FINISH

MATERIAL  
SEE TABLE  
-

27 FEB 2004  
-  
-  
-  
PRODUCT SPEC  
108-20256  
APPLICATION SPEC  
-  
WEIGHT  
-

NAME  
3 POS. FASTIN-FASTON Connector  
TAB HOUSING, RAST 5  
0.8-1.0 MM THK. PANEL MOUNT

SIZE  
A2

CAGE CODE  
-

DRAWING NO  
C-293008

RESTRICTED TO  
-

CUSTOMER DRAWING

SCALE  
2:1

SHEET  
2 OF 2

REV  
C1

