


**Product Details for 5051426 - 5**



**5051426 - 5**

[Active](#)

**SHV RF Connectors**

[RoHS Compliant \(Statement of Compliance\)](#)

**Product Highlights:**

- ? Connector
- ? Plug
- ? Coaxial Cable Type (RG/U or Mfg.) = 59, 59A, 59B, 62, 62A, 62B, 124, 140, 210, Belden 9209, Belden 9269, Belden 9291
- ? Coaxial Cable Termination Type = Crimp
- ? Nickel Body Plating

[View all Features](#)

**Quick Links**

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

**Documentation & Additional Information**

**Product Drawings:**

- ? [CONNECTOR, COAXIAL, PLUG, SERIES SHV](#) (PDF, English)

**Catalog Pages/Data Sheets:**

- ? None Available

**Product Specifications:**

- ? None Available

**Application Specifications:**

- ? None Available

**Instruction Sheets:**

- ? None Available

**CAD Files:**

- ? None Available

**Additional Information:**

- ? [Product Line Information](#)

**Related Products:**

- ? [Tooling](#)

[List all Documents](#)

**Product Features** (Please use the Product Drawing for all design activity)

**Product Type Features:**

- ? [Product Type](#) = Connector
- ? [Gender](#) = Plug
- ? Crimp Type = Dual
- ? Dielectric Material = TEFLON

**Mechanical Attachment:**

- ? Panel Attachment = Without

**Termination Related Features:**

- ? Coaxial Cable Termination Type = Crimp

**Body Related Features:**

- ? [Body Plating](#) = Nickel

**Contact Related Features:**

- ? Center Contact Plating = Gold

**Configuration Related Features:**

- ? [Coaxial Cable Type \(RG/U or Mfg.\)](#) = 59, 59A, 59B, 62, 62A, 62B, 124, 140, 210, Belden 9209, Belden 9269, Belden 9291

**Industry Standards:**

- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Not relevant for lead free process
- ? RoHS/ELV Compliance History = Always was RoHS compliant

**Conditions for Usage:**

- ? Terminate To = Coaxial Cable

**Other:**

- ? Brand = AMP