


## FST-22A-12 Product Details

[Live Product Chat](#)



### FLEXSTRIP® Jumpers

[Always EU RoHS/ELV Compliant](#) ([Statement of Compliance](#))

#### Product Highlights:

- 2.54 mm Centerline
- Teflon Insulation Material
- Insulation Length = 50.80 mm
- Pin Arrangement (Left) = A
- Pin Arrangement (Right) = A

[View all Features](#) | [Find Similar Products](#)

### FST-22A-12 (5-1437187-8)

TE Part Number: 5-1437187-8

[Active](#)

[Add to Part List](#)

### Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)
- ▶ [Request Samples](#)

**NEW!**

### Documentation & Additional Information

#### Product Drawings:

- [FLEXSTRIP PIN CONFIGURATIONS, GENERIC](#) (PDF, English)

#### Catalog Pages/Data Sheets:

- None Available

#### Product Specifications:

- None Available

#### Application Specifications:

- None Available

#### Instruction Sheets:

- None Available

#### CAD Files:

- None Available

#### Additional Information:

- [Product Line Information](#)

#### Additional Product Images:

- [Product View](#)
- [Product View](#)

#### Related Products:

- [Tooling](#)

[List all Documents](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- [Insulation Material](#) = Teflon
- [Number of Conductors](#) = 12

#### Electrical Characteristics:

- Current Rating (Amps.) = 3
- Impedance (Ω) = 106
- Voltage Rating (VAC) = 300

#### Body Related Features:

- [Centerline \(mm \[in\]\)](#) = 2.54 [0.100]
- [Insulation Length \(mm \[in\]\)](#) = 50.80 [2.000]

#### Configuration Related Features:

- [Pin Arrangement \(Left\)](#) = A
- [Pin Arrangement \(Right\)](#) = A

#### Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- RoHS/ELV Compliance History = Always was RoHS compliant

#### Conditions for Usage:

- Operating Temperature (°C [°F]) = -40 - +150 [-40 - +302]

#### Other:

- Brand = Tyco Electronics

[Provide Website Feedback](#) | [Need Help?](#)