

Product Details for 5415373 - 1



5415373 - 1

[Active](#)

BNC RF Connectors

[RoHS Compliant](#) [\(Statement of Compliance\)](#)

Product Highlights:

- ? Connector
- ? Connector Type = BNC
- ? Jack
- ? Terminate To Printed Circuit Board
- ? Not Stacked

[View all Features](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- ? [JACK, PCB, RIGHT ANGLE, 75 OHM, BNC](#) (PDF, English)

Catalog Pages/Data Sheets:

- ? None Available

Product Specifications:

- ? [BNC PCB Straight and Right Angle Connectors](#) (PDF, English)

Application Specifications:

- ? None Available

Instruction Sheets:

- ? None Available

CAD Files:

- ? None Available

Additional Information:

- ? [Product Line Information](#)

Related Products:

- ? [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- ? [Product Type](#) = Connector
- ? [Connector Type](#) = BNC
- ? [Gender](#) = Jack
- ? [Stacked](#) = No
- ? [Number of Ports](#) = 1
- ? [PCB Mount Angle](#) = Right Angle
- ? [Grade](#) = Commercial
- ? [PCB Height \(mm \[in\]\)](#) = 10.97 [0.432]
- ? [PCB Retention Feature](#) = With
- ? [PCB Retention Method Feature](#) = Mounting Post
- ? [Mounting Post Style](#) = Standard
- ? Mounting Post Length (mm [in]) = 4.34 [0.171]
- ? [Body Material](#) = Zinc
- ? [Body Insulation](#) = Without
- ? [Sealed](#) = No
- ? [Isolated](#) = No
- ? [Dielectric Material](#) = Polymethylpentene
- ? Solder Terminal = Without

Mechanical Attachment:

- ? Surface Mountable = No
- ? [Panel Attachment](#) = With
- ? Panel Attachment Method = Lockwasher and Nut
- ? Panel Attachment Style = Rear Mount

Electrical Characteristics:

- ? [Connector Impedance \(?\)](#) = 75

Body Related Features:

- ? [Hardware Included](#) = No
- ? [Body Plating](#) = Tin
- ? [Polarized](#) = No
- ? Center Contact Length (mm [in]) = 4.34 [0.171]

Contact Related Features:

- ? [Center Contact Material](#) = Beryllium Copper
- ? [Center Contact Plating](#) = Gold (30)

Industry Standards:

- ? Government/Industry Qualification = No
- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- ? RoHS/ELV Compliance History = Always was RoHS compliant

Conditions for Usage:

- ? [Terminate To](#) = Printed Circuit Board

Other:

- ? Brand = AMP