


Product Details for 558211 - 9



No Image Available

558211 - 9

[Active](#)

Modular Plugs and Accessories

[RoHS Compliant \(Statement of Compliance\)](#)

Product Highlights:

- ? Boot
- ? Boot Type = Standard
- ? Boot Color = Violet

[View all Features](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling Product Feature Selector](#)
- [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- ? [BOOT, MODULAR PLUG](#) (PDF, English)

Catalog Pages/Data Sheets:

- ? None Available

Product Specifications:

- ? None Available

Application Specifications:

- ? [Modular Plug Connectors \(Standard and Small Conductor\)](#) (PDF, English)

Instruction Sheets:

- ? None Available

CAD Files:

- ? None Available

Additional Information:

- ? [Product Line Information](#)

Additional Product Images:

- ? [Product Photo](#)

Related Products:

- ? [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- ? [Product Type](#) = Boot

Termination Related Features:

- ? [Boot Color](#) = Violet

Body Related Features:

- ? Boot Type = Standard
- ? Cable Diameter Range (mm [in]) = 5.58 – 6.10 [0.220 – 0.240]

Industry Standards:

- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Not relevant for lead free process
- ? RoHS/ELV Compliance History = Always was RoHS compliant

Other:

- ? Brand = AMP