

## 569335 -3 Product Details

### 2.16 [.085] IDC Connectors

[RoHS Compliant](#) (Statement of Compliance)

#### Product Highlights:

- ? Strain Relief
- ? Number of Positions = 50
- ? Not Shielded
- ? 90° Cable Exit Angle

[View all Features](#)

#### Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

No Image Available

**569335 -3**

 [Active](#)

#### Documentation & Additional Information

##### Product Drawings:

- ? [COVER KIT, 90 DEGREE, 50 POSITION, CHAMP SYSTEM 5](#) (PDF, English)

##### Catalog Pages/Data Sheets:

- ? None Available

##### Product Specifications:

- ? None Available

##### Application Specifications:

- ? None Available

##### Instruction Sheets:

- ? None Available

##### CAD Files:

- ? None Available

##### Additional Information:

- ? [Product Line Information](#)

##### Additional Product Images:

- ? [Product Photo](#)

##### Related Products:

- ? [Tooling](#)

[List all Documents](#)

#### Product Features

(Please use the Product Drawing for all design activity)

##### Product Type Features:

- ? [Product Type](#) = Strain Relief
- ? [Number of Positions](#) = 50
- ? [Shielded](#) = No

##### Body Related Features:

- ? [Cable Exit Angle](#) = 90°

##### Industry Standards:

- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Not relevant for lead free process
- ? RoHS/ELV Compliance History = Always was RoHS compliant

##### Operation/Application:

- ? Application = System 5

##### Other:

- ? Brand = AMP