

61148-1 Product Details

[Live Product Chat](#)



61148-1

TE Part Number: 61148-1

[Active](#)

[Add to Part List](#)

Miscellaneous Terminals

[Always EU RoHS/ELV Compliant](#) ([Statement of Compliance](#))

Product Highlights:

- Brush Contact
- Insulation Support
- Wire Range = 0.68-1.19² [22-17] mm [AWG]
- Not For Use With Double Wire
- Phosphor Bronze Material

[View all Features](#) | [Find Similar Products](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)
- ▶ [Request Samples](#)

NEW!

Documentation & Additional Information

Product Drawings:

- [amplivar brush contact](#) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Product Type = Brush Contact
- [Insulation Support](#) = Insulation Support
- Material = Phosphor Bronze
- Finish = None
- Insulation Diameter (mm [in]) = 2.41-2.92 [.095-.115]
- Proprietary Name = AMPLIVAR

Body Related Features:

- [Wire Range \(mm \[AWG\]\)](#) = 0.68-1.19² [22-17]
- Double Wire = No
- Stock Thickness (mm [in]) = 0.51 [0.020]

Contact Related Features:

- Bulb = Without

Configuration Related Features:

- Diode = Without

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

Packaging Related Features:

- Packaging Method = Strip

Other:

- Brand = AMP

[Provide Website Feedback](#) | [Need Help?](#)