



+ TERMINALS & SPLICES

QUICK DISCONNECTS



✓ Active

TE CONNECTIVITY (TE)

TERMINAL FASTON .250 TAB 22-18 AWG BR

FASTON | 250

626377-1

TE Internal Number: 626377-1

EU RoHS Compliant with Exemptions

EU ELV Compliant with Exemptions

Terminal Type Tab

Wire Size (AWG) 22 – 18

Wire Size (mm²) .3 – .8

Mating Tab Width 6.35 mm [.25 in]

Mating Tab Thickness .81 mm [.032 in]

 **PRODUCT DRAWING**
English

 **3D PDF**

DOCUMENTATION

Product Drawings

TERMINAL FASTON .250 TAB

PDF

English

CAD Files

3D PDF

PDF

3D

Customer View Model

2D_DXF.ZIP

English

Customer View Model

3D_IGS.ZIP

English

Customer View Model

3D_STP.ZIP

English

Product Environmental Compliance

TE Material Declaration

MD_626377-1_06292015134_dmtec

PDF

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Terminates To Wire & Cable

FASTON Yes

Insulated Wire Support Yes

Disconnect Type Quick Connect

Insertion Force Normal

Insulated No

Wire/Cable Type Discrete Wire

Wire Stop No

Wire/Cable Composition Stranded

Body Features

Fully Insulated Yes

Plating Material Unplated

Contact Features

Terminal Type Tab

Terminal Orientation Straight

Barrel Type Open

Crimp Type F-Crimp

Mechanical Attachment

Mating Retention Type Hole

Dimensions

Wire Size (AWG) 22 – 18

Wire Size (mm²) .3 – .8

Mating Tab Width 6.35 mm [.25 in]

Mating Tab Thickness .81 mm [.032 in]

Accepts Wire Insulation Diameter Range 2 – 3 mm [.08 – .118 in]

Wire Insulation Diameter (Max) 3 mm [.118 in]

Overall Length 19.3 mm [.76 in]

Industry Standards

CSA Certified Yes

UL Rating Recognized

Packaging Features

Packaging Method Reel

Packaging Quantity 8000

PRODUCT COMPLIANCE



Statement of Compliance

Statement of Compliance

PDF
