

 [Live Product Chat](#)



Not reviewed for RoHS Compliance

- Barrier Strip
- Barrier Style = Single Row, Tri-Barrier
- Block Style = Open Bottom with Standoffs
- 11.10 mm Centerline
- Vertical Mount Angle

[View all Features](#) | [Find Similar Products](#)

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

 Obsolete

[Add to Part List](#)
[Contact Product](#)
[Information Center](#)

Product Drawings: • None Available Catalog Pages/Data Sheets: • None Available Product Specifications: • None Available Application Specifications: • None Available Instruction Sheets: • None Available CAD Files: • None Available	Additional Information: • Product Line Information Related Products: • Tooling
---	--

Product Features (Please use the Product Drawing for all design activity)

Termination Related Features:

- [Product Type](#) = Barrier Strip
- [Mount Angle](#) = Vertical
- Number of Positions = 4
- CSA File No. = LR30811
- UL Recognized = File No. E54800
- Screw Material = Steel
- Mounting Ears = Without
- Comment = Do not order Screw and Captive Clamp in combination with other top hardware.; Other options available upon request, consult our Product Information Center.

- Terminal Plating = Bright Tin

- Terminal Plating = Bright Tin

- Barrier Style = Single Row, Tri-Barrier
- Block Style = Open Bottom with Standoffs
- Centerline (in [mm]) = 0.4375 [11.10]
- Number of Rows = Single
- Terminal Style = Solder Turret 8.40 [.331]
- Terminal Material = Copper Alloy

- Mounting Options = None

- RoHS/ELV Compliance = Not reviewed for ELV/RoHS compliance
- Lead Free Solder Processes = Not reviewed for lead free solder process

Other:

- Top Hardware = Wire Clamp Combo Head
- Number of Levels = Single
- End Barriers = Without
- Bracket = Without
- Current Rating (Amps.) = 30
- Screw Head Type = Slotted
- Voltage (VAC) = 600
- Mounting Insert = Without

- Brand = Buchanan