

## 9-221128-1 Product Details

[Live Product Chat](#)**9-221128-1**

TE Internal Number: 9-221128-1

**Superseded**[Search for Replacement Parts](#)


### BNC RF Connectors


[Always ELV Compliant](#) ([Find RoHS Compliant Alternates/Statement of Compliance](#))

#### Product Highlights:

- Connector
- Connector Type = BNC
- Plug
- Terminate To Coaxial Cable
- Coaxial Cable Termination Type = Crimp

[View all Features](#)

### Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

[Add to My Part List](#)[Request Sample](#)[Find Similar Products](#)[Buy Product](#)

### Documentation & Additional Information

#### Product Drawings:

- [PLUG, COMMERCIAL BNC](#) (PDF, English)

#### Catalog Pages/Data Sheets:

- None Available

#### Product Specifications:

- None Available

#### Application Specifications:

- None Available

#### Instruction Sheets:

- None Available

#### CAD Files: ([CAD Format & Compression Information](#))

- [2D Drawing](#) (DXF, Version AD)
- [3D Model](#) (IGES, Version AD)
- [3D Model](#) (STEP, Version AD)

#### Additional Information:

- [Product Line Information](#)

#### Related Products:

- [Tooling](#)

[List all Documents](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- [Product Type](#) = Connector
- [Connector Type](#) = BNC
- [Gender](#) = Plug
- [Crimp Type](#) = Hex
- [Body Style](#) = Straight
- [Grade](#) = Commercial
- [Body Insulation](#) = Without
- [Sealed](#) = No
- [Isolated](#) = No
- [Dielectric Material](#) = Polyethylene
- [Coupling Nut Material](#) = Brass
- Number of Ports = 1
- Solder Terminal = Without

#### Mechanical Attachment:

- Surface Mountable = No
- Panel Attachment = Without

#### Electrical Characteristics:

- [Connector Impedance \( \$\Omega\$ \)](#) = 50

#### Termination Related Features:

- [Coaxial Cable Termination Type](#) = Crimp

#### Body Related Features:

- [Hardware Included](#) = No
- [Body Plating](#) = Nickel
- [Polarized](#) = No

#### Contact Related Features:

- [Center Contact Material](#) = Brass
- [Center Contact Plating](#) = Gold

#### Configuration Related Features:

- [Coaxial Cable Type \(RG/U or Mfg.\)](#) = 58, 58A, 58B, 58C

#### Industry Standards:

- Government/Industry Qualification = No
- [RoHS/ELV Compliance](#) = ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was ELV compliant

#### Conditions for Usage:

- [Terminate To](#) = Coaxial Cable

#### Other:

- Brand = AMP

[Provide Website Feedback](#) | [Need Help?](#)