


Catalog

- [Home](#)
- [Part Number Search](#)
- [Document Search](#)
- [CAD Model Search](#)
- [Text Search](#)
- [Alternate/Lead Free Part Search](#)
- [Multiple Part Comparison](#)
- [Alphabetical Search](#)
- [Brand Search](#)
- [Industry Product Search](#)
- [Product Type Search](#)
- [Product Family Search](#)
- [Competitor Cross Reference](#)
- [Lead Free Solutions](#)
- [Tool Search](#)
- [Help/Glossary](#)

AMPMODU

↳ .079, .100, .125, & .156 Centerline Crimp-Snap Housings

AMP 926209-3  [Active](#)

**Directive 2002/95/EC
Compliant**

[RoHS Compliant](#)

(Tyco Electronics P/N: 926209-3)

[Search for Parts](#)

Document links for this part cannot be displayed. Your browser does not support inline frames or is currently configured not to display inline frames. Inline frames are supported in both Internet Explorer 5 and Netscape 6, as well as all later versions of these browsers.

Related Part Information		
General Information	eCommerce	Related Part Information
<ul style="list-style-type: none"> » General Info » Sales Info » Assembly Subcontractors 	<ul style="list-style-type: none"> » Pricing » Product Availability 	<ul style="list-style-type: none"> » Tooling

Searchable Features:	
Brand:	AMP
RoHS/ELV Compliance:	RoHS compliant, ELV compliant
Lead Free Solder Process:	Not reviewed for lead free solder process
No. of Positions:	6
No. of Rows:	Dual
Housing Configuration:	Both Ends Closed
Centerline, Matrix (mm [in]):	2.54 [.100]
Contact Type:	Locking Clip
Mating Polarization:	No
Mating Connector Lock:	Without
Strain Relief:	Without

Other Properties:	
RoHS/ELV Compliance History:	Always was RoHS compliant
Housing Flammability Rating:	UL 94V-0
Stamped:	No
Housing Color:	Black

Keyed:	No
Housing Material:	Glass-Filled PBT

[Copyright](#) and [Privacy Statement](#)

Visit [Tyco International, Ltd.](#)

[Products](#) | [Catalog](#) | [Brands](#) | [Industries](#) | [Commerce](#) | [Supplier](#) | [Contact Us](#) | [About](#) | [Home](#)