






Montagehinweis



^x Abstand für sichere Kontaktgabe max: 21 mm





Notes,

1 Material, insert: PC
UL-File Nr.: E101788(R)

2 Finisch: contact Ag

Bemerkungen,
 1 Material: Einsatz: PC
 UL-File Nr.: E101788(R)
 2 Oberfläche: Kontakte Ag



1	Stifteinsatz HB24		hellbeige	1	-
1-1	DESCRIPTION / BENENNUNG	MATERIAL	COLOR / FARBE	ITEM NO. POS.	REMARKS / BEMERKUNGEN
HB.24.Sti.S ORDERING TEXT / BESTELLTEXT	THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION. DIESER ZEICHNUNGSDOCUMENT WIRD DURCH AMP INCORPORATED KONTROLLIERT. AENDERUNGEN, DIE DEM TECHNISCHEN FORTSCHRITT DIENEN, SIND VORBEHALTEN. DEN JEWEILIG LETZTGELTEFEN AENDERUNGSSTAND ERFAEHRN SIE AUF AMRAGE.			DWN 06.09.01 Schneider	 HTS Elektrotechnik 53819 Neunkirchen, Germany
				CHK 06.09.01 Schweiger	
	DIMENSIONS: DIMENSIONEN: mm			APVD -	NAME
				PRODUCT SPEC PRODUKTSPEZ.	Male insert
	TOLERANCES UNLESS OTHERWISE SPECIFIED: ALL GEMEINTOLERANZEN			-	Stifteinsatz HB.24.Sti.S
	n. ISO 8015 n. ISO 2768 - mH - E n. DIN 16901 - 140			APPLICATION SPEC VERARBEITUNGSSPEZ.	SIZE
	0 PLC - 1 PLC - 2 PLC - 3 PLC -			-	CAGE CODE
	ANGLES /WINKEL #-			WEIGHT GEWICHT -	DRAWING NO ZEICHNUNGS-NR.
	MATERIAL			CUSTOMER DRAWING	RESTRICTED TO NUR FUER
	FINISH / OBERFLAECHE / FARBE			/ KUNDENZEICHNUNG	MASSSTAB 1:1
				BLATT 1	
				OF 1	
				REV A1	