

## 925369-2 Product Details

Have a Question?

Chat with a Product Information Specialist



925369-2

TE Internal Number: 925369-2

 Active

 [View 3D PDF](#)

### .100 AMPMODU Headers, Housings & Contacts

 [Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

#### Product Highlights:

- Connector
- Housing
- Connector Style = Receptacle
- Contact Type = Receptacle
- 2.54 mm Centerline

[View all Features](#)

#### Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

 [Add to My Part List](#)  [Request Sample](#)  [Find Similar Products](#)  [Buy Product](#)

### Documentation & Additional Information

#### Product Drawings:

- [AMPMODU IV GEH A USE,EINREIHIG](#) (PDF, English)

#### Catalog Pages/Data Sheets:

- None Available

#### Product Specifications:

- [Interconnection System, AMPMODU Mod IV 1/2](#) (PDF, English)

#### Application Specifications:

- None Available

#### Instruction Sheets:

- None Available

#### CAD Files: ([CAD Format & Compression Information](#))

- [2D Drawing](#) (DXF, Version U1)
- [3D Model](#) (IGES, Version U1)
- [3D Model](#) (STEP, Version U1)

[List all Documents](#)

#### Additional Information:

- [Product Line Information](#)

#### Related Products:

- [Tooling](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- Product Type = Connector
- Connector Type = Housing
- [Termination Method to Wire/Cable](#) = Crimp
- [Mating Connector Lock](#) = Without
- Mating Polarization = Without
- [Strain Relief](#) = With
- [Connector Series](#) = Mod IV
- [Keyed](#) = No
- Housing Configuration = Both Ends Closed

#### Body Related Features:

- Centerline (mm [in]) = 2.54 [0.100]
- Row-to-Row Spacing (mm [in]) = 2.54 [0.100]
- [Number of Positions](#) = 2
- [Number of Rows](#) = 1

#### Contact Related Features:

- Contact Type = Receptacle

#### Housing Related Features:

- Connector Style = Receptacle
- [Housing Color](#) = Green
- UL Flammability Rating = UL 94-HB
- Housing Material = Nylon

#### Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

#### Packaging Related Features:

- Packaging Quantity = 100

#### Other:

- Brand = AMP

 BOOKMARK 

#### Corporate Information

[Who We Are](#)  
[Investors](#)  
[News Room](#)  
[Supplier Portal](#)  
[Careers](#)

#### Quick Links

[Check Distributor Inventory](#)  
[Cross Reference](#)  
[Find Documents & Drawings](#)  
[Product Compliance Support Center](#)  
[Site Map](#)

#### Customer Support

[Email or Chat with Us](#)  
[Find a Phone Number](#)  
[Search Knowledge Base](#)  
[Manage Your Account](#)

#### Sign up for our eNewsletter

Enter your email address 

#### Follow Us On:



Visit Us On:

