

## 282706-1 Product Details

[Share](#) [Print](#) [Email](#)


282706-1

TE Internal Number: 282706-1  
✔ [Active](#)

### Econoseal J Series [Mark II (+)]

[Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

#### Product Highlights:

- Econoseal J Product Line
- 070 Series
- Accessory
- Wire-to-Wire / Wire-to-Panel
- Accessory Type = Double Lock Plate

[View all Features](#)

[Add to My Part List](#)
[Request Sample](#)
[Find Similar Products](#)
[Buy Product](#)

#### Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

### Documentation & Additional Information

**Product Drawings:**

- [3 POS. DOUBLE LOCK PLATE FOR PLUG HSG ECONOSEAL J-MK...](#) (PDF, English)

**Catalog Pages/Data Sheets:**

- None Available

**Product Specifications:**

- None Available

**Application Specifications:**

- None Available

**Instruction Sheets:**

- [3 w. AMP Econoseal J-MKII+ plug conn.](#) (PDF, English)

**CAD Files:**

- None Available

**Additional Information:**

- [Product Line Information](#)

**Related Products:**

- [Tooling](#)

[List all Documents](#)

### Product Features (Please use the Product Drawing for all design activity)

**Product Type Features:**

- Product Line = Econoseal J
- Series = 070
- [Product Type](#) = Accessory
- [Accessory Type](#) = Double Lock Plate
- For Use With = Plug (Receptacle) Housing
- Accessory Color = Red

**Body Features:**

- Number of Rows = 1
- Centerline (mm [in]) = 4.80 [0.1889]
- Number of Positions = 3
- Accessory Material = PBT

**Housing Features:**

- UL Flammability Rating = UL 94-HB

**Industry Standards:**

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant
- IP Water Sealing Level = IEC 529 IP X.4

**Environmental:**

- Operating Temperature (°C [°F]) = -30 - +105 [-22 - +221]

**Operation/Application:**

- Application Use = Wire-to-Wire / Wire-to-Panel

**Packaging Features:**

- Packaging Method = Box
- Packaging Quantity = 12,000

**Other:**

- GET 0.64 Connector System = No
- Brand = AMP

#### Corporate Information

- [Who We Are](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)

#### Quick Links

- [Check Distributor Inventory](#)
- [Cross Reference](#)
- [Find Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

#### Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Search Knowledge Base](#)
- [Manage your Account](#)

#### Keep Me Informed

Receive TE News, Events & Technology Updates

