






LOC		DIST		REVISIONS			
P	LYR	DESCRIPTION		DATE	DWN	APVD	
		1	PROPOSED	11 JUN 2009	RW	RB	
		A	RELEASED PER ECO-09-017979	03 AUG 2009	DD	RB	



SECTION A-A



1. ELBOW DESIGN ALLOWS FOR 360° EXIT ROTATION

16.5	10.6	45.8	27.7	22.2	22.5	17.0	13	16	6	1-2098436-2
16.5	10.6	43.8	27.7	22.2	20.6	15.1	13	16	4	1-2098436-1
13.5	7.2	42.1	27.7	22.2	22.5	17.0	10	12	6	1-2098436-0
13.5	7.2	40.1	27.7	22.2	20.6	15.1	10	12	4	2098436-9
10.4	7.2	42.1	27.7	22.2	22.5	17.0	7.5	08	6	2098436-8
10.4	7.2	40.1	27.7	22.2	20.6	15.1	7.5	08	4	2098436-7
16.5	10.6	42.7	27.3	21.6	17.1	11.6	13	16	3	2098436-6
16.5	10.6	40.2	23.2	17.5	17.0	11.6	13	16	2	2098436-5
13.5	7.2	39.0	27.3	21.6	17.1	11.6	10	12	3	2098436-4
13.5	7.2	36.5	23.2	17.5	17.0	11.6	10	12	2	2098436-3
10.4	7.2	39.0	27.3	21.6	17.1	11.6	7.5	08	3	2098436-2
10.4	7.2	36.5	23.2	17.5	17.0	11.6	7.5	08	2	2098436-1
G	F	E	D	C	B	A	NW NC CONDUIT SIZE		CONNECTOR POSITIONS	TYCO ELECTRONICS PART NO.

DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		DWN	11 JUN 2009	Tyco Electronics Harrisburg, PA 17105-3608	
mm		9 PLC ±.5 1 PLC ±.5 2 PLC ±.5 3 PLC ±.5 4 PLC ±.5 ANGLES ±1°		CHK	11 JUN 2009		
MATERIAL		FINISH		APVD	11 JUN 2009	NAME BACKSHELL, RIGHT-ANGLE, LOW PROFILE CAP CONNECTOR, NW/NC CONDUIT AMPSEAL 16	
NYLON 6/6, BLACK				PRODUCT SPEC			
				APPLICATION SPEC		SIZE CAGE CODE DRAWING NO	
				WEIGHT			
				CUSTOMER DRAWING		A100779C=2098436	
						RESTRICTED TO	