© 2019 TE Connectivity. All Rights Reserved.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A2	ECR-09-013545	12MAY2009	SR	AR
	A3	REVISED PER ECR-17-013084	08JAN2018	NC	MKO
	A4	REVISED PER ECR-19-007853	17MAY2019	SR	JB


NOTES


1 PART SHALL BE FREE AND CLEAN OF BURRS AND OTHER FOREIGN MATERIAL


2 PACKAGING: QUANTITY 3 PIECES


3 VARNISHING INSIDE HOUSING NOT REQUIRED


△4 OBSOLETE PARTS














△4	△4							
	1		O-RING	NEOPRENE		BLACK	10	PG29
	1		ADAPTOR	BRASS	NICKEL PLATED	BLUE	9	PG29
1		1	ADAPTOR ROUND	BRASS	NICKEL PLATED	BLUE	8	PG29
2			SLIDE SPOOL	STEEL	ZINC PLATED	BLUE	7	
2			CLIP BOLT	STEEL	ZINC PLATED	BLUE	6	
	4		CLIP BOLT	STAINLESS STEEL	BLANC		5	
		4	CLIP BOLT	STEEL	ZINC PLATED	BLUE	4	
1			HOOD	ALUMINIUM		GREY	3	
	1		HOOD	ALUMINIUM	ALUMINIUM OXID	BLACK	2	
		1	HOOD	ALUMINIUM		GREY	1	
1-7	2-6	1-6	DESCRIPTION	MATERIAL	SURFACE	COLORE	ITEM	NOTES
			~~HB.32.STS.1.29.Z~~					
			~~HB-K.32.STS.1.29.Z~~					
			HB.32.STS-GR.1.29.Z					

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN R.SCHNEIDER 12MAY2009
CHK T.SCHNURPFEIL 12MAY2009
APVD -
PRODUCT SPEC -
APPLICATION SPEC -
WEIGHT -

TE Connectivity

NAME HOOD
HB.32.STS.1.29.Z
-

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±
4 PLC ±
ANGLES ±1°

MATERIAL - -
FINISH - -

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A2	00779	C-1102347	

CUSTOMER DRAWING | SCALE 1:1 | SHEET 1 OF 1 | REV A4