





SECTION AA-AA


SECTION BB-BB




DETAIL CC



MATING DETAIL



RECOMMENDED PC BOARD FOOTPRINT (COMPONENT SIDE)



RECOMMENDED PANEL OUTPUT

- ▲ MATERIAL & FINISH :
- CONTACT : COPPER ALLOY, Au PLATE IN CONTACT AREA
 - Sn-Pb PLATE IN TINE OVER Ni PLATE
 - HOUSING : LIQUID CRYSTAL POLYMERS
 - TINE PLATE : LIQUID CRYSTAL POLYMERS
 - SHELL : STEEL, Ni PLATE
 - RETENTION LEG : BRASS, Sn-Pb PLATE
- ▲ DATUMS AND DIMENSIONS ESTABLISHED BY CUSTOMER.
- ▲ LONGEST LOADED CONTACTS
(8 TOTAL : PIN NO. 4n+1, 4n+2, 5n-1, 5n, 5n+1, 5n+2, 6n-1, 6n)
- ▲ SHORTEST LOADED CONTACTS
(2 TOTAL : PIN NO. 3n+2, 4n)
- ▲ GENERAL LOADED CONTACTS, EXCEPT NOTE ▲, ▲

| | | | | | | | | | |
|-----|------|------|------|------|-------|------|----|------|-----------|
| 3.4 | 59.7 | 59.0 | 66.6 | 53.0 | 56.23 | 75.0 | 50 | 300 | 1-11315-5 |
| 2.8 | 37.7 | 37.0 | 44.6 | 31.0 | 34.23 | 53.0 | 28 | 168 | 1-11315-4 |
| 2.8 | 43.7 | 43.0 | 50.6 | 37.0 | 40.23 | 59.0 | 34 | 204 | 1-11315-3 |
| 2.8 | 49.7 | 49.0 | 56.6 | 43.0 | 46.23 | 65.0 | 40 | 240 | 1-11315-2 |
| 2.8 | 59.7 | 59.0 | 66.6 | 53.0 | 56.23 | 75.0 | 50 | 300 | 1-11315-1 |
| H | F | E | D | C | B | A | n | PSQL | PART NO. |

| | | | | | |
|--|------------------|--|-------|--|----------|
| © 1986 BY AMP MANUFACTURING TAIWAN LTD. ALL RIGHTS RESERVED. PRODUCTS ARE COVERED BY PATENTS AND/OR PATENTS PENDING. | | | | AMP AMP MANUFACTURING TAIWAN LTD. | |
| OVER RANGE | OPERATION DIA | DESCRIPTION PLUG ASS'Y, V TYPE, W/O DRAIN-WIRE, 1 mm DOCKING CONNECTOR | | | |
| MATERIAL | FINISH | GENERAL TOLERANCE | SEC | LOC | QTY |
| ▲ | ▲ | A3 | DW | | C-11315 |
| ECN NO. PV00-1066-98 S L J Y 1986 ECN NO. PV00-0204-96 J Y J C 1986 ECN NO. PV00-0143-96 J Y J C 1986 RELEASED J Y J C 1986 | | DECIMAL: ± 0.25 | SHEET | REV | SCALE |
| LTR. | REVISION REQUIRE | DR. | CHK. | DATE | 1 OF 1 C |

(CUSTOMER DRAWING)

DIMENSIONS IN mm. DO NOT SCALE PRINT.