



All Signal Relays: 5 Amp, Monostable DC (0)

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JAN 2023 (233) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought



TE Part #T1280242132-000
H24B-TGBH-M32



TE Part #20017615-05
VCS-05 Liquid Level Sensor



TE Part #961931-000
207W213-25-G01-0



TE Part #8-1415899-8
RZ01-1A3-D009



TE Part #4-1879127-0
RN 0402 340R 0.1% 10PPM CUT
LENGTH




TE Part #2057833-1
SFP+ Enhanced 1x4 Cage Assy



TE Part #2213765-7
AV19 SPM 3A SPOT LED RED 24V



TE Part #2-1624116-6
BMB-A 0603 40R N8



TE Part #1051810-1
SMA CABLE PLUG 2031 8125 92



TE Part #2007793-3
IMP100S,H,V3P16C,LG,OEW39,5,5

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-1393809-4_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-1393809-4_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-1393809-4_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Definitions General Purpose Relays

English

Product Specification

English

