


REV. 0

DCO 141815

COIL: @ 25°C

RESISTANCE	1560 OHMS ±10%
NOMINAL VOLTAGE	26.5 VDC
MUST OPERATE	15.2 VDC
MUST RELEASE	9.5 VDC MAX, 1.8 VDC MIN.

ENVIRONMENT:

VIBRATION 10 CPS TO 3000 CPS @ 30 g's

SHOCK 75 g's 6 MS. DURATION


TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE TIME 2.0 MS MAX

RELEASE TIME 4.0 MS MAX

CONTACT STABILIZATION 2.0 MS MAX

CUSTOMER DATA SHEET



TERMINAL VIEW

CONTACT RATING: LOW LEVEL TO 1A 28 VDC RESISTIVE 100,000 OPERATIONS

DR. B.D. 2/28/00 CK 2/28/00

COMMUNICATIONS INSTRUMENTS, INC.

CUST. QPL

CUST. NO. M39016/20-078P REV.

"JMADD" RELAY

JMACDD-26XPS2