416PA503M × OBSOLETE

Citec

TE Internal #: 1-1623894-3

TE Internal Description: 416P 50K

View on TE.com >



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUL 2021 (219) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Wave solder capable to 240°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Customers Also Bought



TE Part #YCFX20F2532SZN0000

RECP ASSY




TE Part #627933-000

TXR40AC00-1207AI




TE Part #3827513001

44A1121-22-0/2-9



TE Part #8819823001

55A0131-20-0/2/9




TE Part #2-1879252-5
RP 2B 5R76 0.1% 15PPM CUT LENGTH



TE Part #Y5015-000000078029
LOCKING BACK NUT



TE Part #7-1625876-6
CBT 1/2 5% 220R BULK



TE Part #CQ06573001
44A1231-10-9/93/96-9

Documents

Datasheets & Catalog Pages

1309350_PASSIVE_COMPONENT

English

Type 416 Series Economy Trimmers

English