


1-171433-2 ✓ ACTIVE

TE Internal #: 1-171433-2

TE Internal Description: FF TAB HSG 6P NYLON RED

[View on TE.com >](#)



Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Customers Also Bought




TE Part #170092-4
FF 250 REC 18-14AWG TPBR
REREELING




TE Part #170330-1
PL MKII 187 REC 24-20AWG PTBR LP




TE Part #171432-1
FF 250 REC HSG 6P NYLON NAT



TE Part #171433-1
FF 250 TAB HSG 6P NYLON NAT



TE Part #1-171433-6
FF TAB HSG 6P NYLON BLUE



TE Part #172074-1
187 HSG. PLMKII REC. NAT



TE Part #350547-1
UMNL PIN 20-14 PTPBR L/P



TE Part #350550-1
UMNL SOK 20-14 PTPBR L/P



TE Part #1-480698-0
02P UMNL PLUG HSG NATL



TE Part #1-480699-0
02P UMNL CAP HSG NATL

Documents

Product Drawings

FF TAB HSG 6P NYLON RED

Japanese

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_1-171433-2_D.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-171433-2_D.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-171433-2_D.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Agency Approvals



CSA Certificate

English