RL73H2ER27FTD ✔ ACTIVE

CGS | CGS RL73

TE Internal #: 1-1879463-1

27 ohm, Thick Film, Current Sensing Resistor, 1 %, 1210, .5 W, ±100 ppm/°C, Solder, 2 Terminations, .55 mm [.022 in] Height, CGS RL73

View on TE.com >

Passive Components > Resistors > Surface Mount Resistors > Thick Film Resistor: Current Sense



Resistor Type: **Current Sensing Resistor**

Element Type: **Thick Film**

Package Size Code: **1210**

Power Rating: **.5 W**

Resistance Value: **27 Ω**

All Thick Film Resistor: Current Sense (434)

Features

Product Type Features

Resistor Type	Current Sensing Resistor
Element Type	Thick Film
Package Size Code	1210

Configuration Features

Number of Resistors	1

Electrical Characteristics

Power Rating	.5 W
Resistance Value	27 Ω
Resistance Class	Up to 1kΩ
Passive Component Tolerance	1 %

Termination Features

Surface Mount Resistor Termination Type	Solder
Number of Terminations	2

Dimensions

Product Height	.55 mm[.022 in]
Product Length	3.1 mm[.122 in]
Product Width	2.6 mm[.102 in]

Usage Conditions

Temperature Coefficient	±100 ppm/°C

Packaging Features

Packaging Method	Taped & Reeled

Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量超出标准 Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts




TE Part # CAT-C339-R529
Thick Film Resistor: Current Sense




TE Part # 6-1622824-1
RL73N 1J R10 5% 5K RL

Also in the Series | CGS RL73



Surface Mount Resistors(472)

Customers Also Bought



TE Part #214782-E
EPSVA KS GDM4 EE 10 3,8 SN * STROMVERSOR



TE Part #641976-1
15P UMNL PIN HDR ASSY POL 94VO



TE Part #4-794630-0
10POS MICRO MNL ASSY,VRT,HDR




TE Part #3-794680-2
02P MICRO MNL ASSY,VRT,THRU LF



TE Part #3-794680-4
04P MICRO MNL ASSY,VRT,THRU LF




TE Part #3-1415899-5
RZ02-1C4-D012




TE Part #5-1879267-0
RP 2B 1M0 0.1% 15PPM 1K RL



TE Part #4-2176330-5
CRGP 2010 47K 1%



TE Part #1-2176331-4
CRGP 2512 120R 1%



TE Part #2176350-6
CRGCQ 2512 6R8 5%

Documents

Product Drawings

RL73H 2E R27 1% 5K RL

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-1879463-1_BA.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-1879463-1_BA.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-1879463-1_BA.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Datasheets & Catalog Pages

SMD Low Ohmic Current Sense Resistors - Type RL73 Series

English