





1. WILL ACCEPT (12) MULTIMATE AND (4) TYPE XII PIN CONTACTS.

2. CAVITY IDENTIFICATION ON FRONT AND REAR FACE.

3. NO. 4 FASTENERS RECOMMENDED FOR MOUNTING.

4. THIS CONNECTOR WILL ACCEPT INSULATION DIAMETERS UP TO 3.81 [1.50].

HOUSING: NYLON, BLACK.

PERIPHERAL SEAL: ELASTOMER, BLACK.

THREADED INSERT: BRASS

PERMANENT WHITE MARKED OR WHITE INK STAMPED CAVITY IDENTIFICATION.

HOUSING: NYLON, RED.

PERIPHERAL SEAL: ELASTOMER, GRAY.

WHITE DOT NEAR POSITION 1 ON WIRE ENTRY FACE.
- TE LOGO AND PART NUMBER LOCATED ON ANY FLANGE EDGE

	5	#4-40 THREADED INSERTS	NO	A	1-207486-2
OBsolete	5 8	ø 3.81+/- .08 (.125+/- .003) HOLES	YES	A	1-207486-1
OBsolete	7	ø 3.81+/- .08 (.125+/- .003) HOLES	YES	A	207486-9
PRELIMINARY	6 5	ø 3.81+/- .08 (.125+/- .003) HOLES	YES	A	207486-7
	5	#4-40 THREADED INSERTS	YES	A	207486-6
	5	ø 3.81+/- .08 (.125+/- .003) HOLES	YES	A	207486-5
	5	ø 3.81+/- .08 (.125+/- .003) HOLES	NO	B	207486-2
	5	ø 3.81+/- .08 (.125+/- .003) HOLES	NO	A	207486-1
NOTES		MOUNTING FEATURES	PERIPHERAL SEAL	SEE DETAIL	PART NUMBER
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M. BINNER 05/26/94 CHK R. STONE 6-23-94	TE Connectivity		
DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:	PRODUCT SPEC 108-10024	RECEPTACLE HOUSING, STANDARD SEX, SHELL SIZE 23, CPC		
	0 PLC ± - 1 PLC ± - 2 PLC ± 0.13 [.005] 3 PLC ± - 4 PLC ± - ANGLES ± -	APPLICATION SPEC	SIZE	CAGE CODE	DRAWING NO
MATERIAL	FINISH -	WEIGHT -	A1	00779	207486
CUSTOMER DRAWING		SCALE 2:1	SHEET 1 OF 1	REV U	